

Spherical seating washer **DIN6319** **Ste** **DIN** **Stock**

For M6-M24 screws

RCC RCX

- Use a concave washer with a convex washer
- Material:
Treated steel, tempered,
Manganese phosphating
- Other sizes on request






RCX



RCC

Advantages

- Good distribution of clamping force
- Ensures that the screw head is in the right position



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	Net	-5%	-10%	On request

Part number	For screw	ØD1 H13	ØD3	ØD5	H1	H2	R1	Max static load (kN)	Stock*	Price each 1 to 5
Convex washer										
RCX-6	M6	6,4	12	-	0,7	2,3	9	9	✓	0,92 €
RCX-8	M8	8,4	17	-	0,6	3,2	12	17	✓	0,95 €
RCX-10	M10	10,5	21	-	0,8	4	15	26	✓	1,31 €
RCX-12	M12	13	24	-	1,1	4,6	17	38	✓	1,67 €
RCX-14	M14	15	28	-	1,4	5	22	53	-	2,38 €
RCX-16	M16	17	30	-	1,3	5,3	22	73	-	2,38 €
RCX-20	M20	21	36	-	2	6,3	27	117	-	3,60 €
RCX-24	M24	25	44	-	2,4	8,2	32	168	-	5,38 €
Concave washer										
RCC-6	M6	7,1	12	11	-	2,8	-	9	✓	0,99 €
RCC-8	M8	9,6	17	14,5	-	3,5	-	17	✓	1,10 €
RCC-10	M10	12	21	18,5	-	4,2	-	26	✓	1,38 €
RCC-12	M12	14,2	24	20	-	5	-	38	✓	1,74 €
RCC-14	M14	16,5	28	24,8	-	5,6	-	53	-	2,92 €
RCC-16	M16	19	30	26	-	6,2	-	73	-	2,92 €
RCC-20	M20	23,2	36	31	-	7,5	-	117	-	3,95 €
RCC-24	M24	28	44	37	-	9,5	-	168	-	6,02 €

* Subject to available stocks, All dimensions in mm

Our other products



HG5-ECO

Eco range Spur gear,
Steel C45



SH2

Parallel axis helical
gear, Steel 20NCD2



CDP

Flanged drill bushing,
Steel



PDM_PDV

Detectable plastic
palm grip, blue
thermoplastic



SLBE

Indexing plunger -
Spacer, for SLB and SLBS index
bolts



RBNpl

Swivel castor with
double brake, Steel -
rubber



PPG

Indexing plunger with
flange, with
horizontal mounting
flange



AT5M AT10M

AT type timing belt
per metre, AT10 Steel
cored polyurethane



V3RA_PT

3-spoked handwheel
with handle,
Polyamide



AT5courroie

AT type timing belt,
AT5 Steel cored
polyurethane



CHT

Asynchronous AC
Motor, 0.18 to 0.55kW



CHA60

Rectangular hinge,
drilled or countersunk,
Rectangular, drilled or
C...

Complementary products



RCX-6

Spherical tilt washer -
DIN6319, convex



RCC_RCX

Spherical tilt washer -
DIN6319, concave



RCC_RCX

Spherical tilt washer -
DIN6319, convex