

Sealing brush strip



STRIP Straight rigid support 1 metre

1m

- Provides a seal for the bottoms of doors, gates or roller shutters
- Prevents rodent entry
- Materials:
 - Frame: anodised aluminium
 - Brush: black polypropylene fibres with anti-UV treatment


Option

- Can be modified to order (subject to min quantity)

Aluminium strip



Can be modified to order



DISCOUNTS

Qty	1+	6+	25+	50+
Disc.	List	-10%	-15%	On request

Part number	Length (mm)	FH	H	B	C	E	Stock*	Price each 1 to 5
STRIP3-15-1000	1000	15	15	6,2	6,5	1,2	✓	14,05 €
STRIP3-20-1000	1000	20	15	6,2	6,5	1,2	✓	15,13 €
STRIP3-25-1000	1000	25	15	6,2	6,5	1,2	✓ New	16,53 €
STRIP5-25-1000	1000	25	25	8	8	1,2	✓	17,11 €
STRIP5-30-1000	1000	30	25	8	8	1,2	✓	17,71 €
STRIP5-40-1000	1000	40	25	8	8	1,2	✓ New	20,87 €
STRIP5-50-1000	1000	50	25	8	8	1,2	✓ New	22,16 €
STRIP8-40-1000	1000	40	50	13	13	2	✓	26,88 €
STRIP8-60-1000	1000	60	50	13	13	2	✓	33,08 €
STRIP8-80-1000	1000	80	50	13	13	2	✓	37,44 €
STRIP8-120-1000	1000	120	50	13	13	2	✓ New	69,59 €
STRIP8-150-1000	1000	150	50	13	13	2	✓ New	80,39 €

*Depending on availability - Dimensions in mm



Straight rigid support 3 meters

STRIP
3m

- Provides a seal to the bottoms of doors, gates or roller shutters
- Prevents rodent entry
- Materials :
Frame : anodized aluminium
Brush : black polypropylene fibres

Aluminium strip

Can be modified to order



DISCOUNTS

Qty	1+	4+	6+	10+
Disc.	List	-10%	-15%	On request

Part number	Length L (mm)	A	B	C	H	S	Stock*	Price each 1 to 3
STRIP5-25	3000	17	8,0	8	25	25	✓	51,42 €
STRIP8-80	3000	37	12,6	13	50	80	✓	112,49 €

*Depending on availability - Dimensions in mm

Sealing brush strip




STRIP Right angled rigid support 1 meter

1M

- Provides a seal for the bottoms of doors, gates or roller shutters
- Prevents rodent entry
- Material :
 Frame : anodised aluminium
 Brush : black polypropylene fibres with anti-UV treatment

Option

- Can be modified to order (subject to min quantity)



DISCOUNTS

Qty	1+	6+	25+	50+
Disc.	List	-10%	-15%	On request

Part number	Length (mm)	FH	H	B	C	E	Stock*	Price each 1 to 5
STRIP3-15F-1000	1000	15	15	6,5	6,5	1,2	✓	14,05 €
STRIP3-20F-1000	1000	20	15	6,5	6,5	1,2	✓	15,13 €
STRIP5-25F-1000	1000	25	25	8	8	1,2	✓	17,11 €
STRIP5-30F-1000	1000	30	25	8	8	1,2	✓	17,71 €
STRIP8-40F-1000	1000	40	50	13	13	2	✓	26,88 €
STRIP8-60F-1000	1000	60	50	13	13	2	✓	33,08 €
STRIP8-80F-1000	1000	80	50	13	13	2	✓	37,44 €

*Depending on availability - Dimensions in mm