

Sealing brush strip



STRIP 1m


Straight rigid support 1 metre

- Provides a seal for the bottoms of doors, gates or roller shutters
- Prevents rodent entry
- Materials:
 - Frame: anodised aluminium
 - Brush: black polypropylene fibres with anti-UV treatment

Option

- Can be modified to order (subject to min quantity)

Aluminium strip



Can be modified to order

DISCOUNTS

| Qty | 1+ | 6+ | 25+ | 50+ |
|-------|------|------|------|------------|
| Disc. | List | -10% | -15% | On request |

| Part number | Length (mm) | FH | H | B | C | E | Stock* | Price each 1 to 5 |
|-----------------|-------------|-----|----|-----|-----|-----|--------|-------------------|
| STRIP3-15-1000 | 1000 | 15 | 15 | 6,2 | 6,5 | 1,2 | ✓ | 13,77 € |
| STRIP3-20-1000 | 1000 | 20 | 15 | 6,2 | 6,5 | 1,2 | ✓ | 14,83 € |
| STRIP3-25-1000 | 1000 | 25 | 15 | 6,2 | 6,5 | 1,2 | - New | 16,20 € |
| STRIP5-25-1000 | 1000 | 25 | 25 | 8 | 8 | 1,2 | ✓ | 16,77 € |
| STRIP5-30-1000 | 1000 | 30 | 25 | 8 | 8 | 1,2 | ✓ | 17,36 € |
| STRIP5-40-1000 | 1000 | 40 | 25 | 8 | 8 | 1,2 | - New | 20,46 € |
| STRIP5-50-1000 | 1000 | 50 | 25 | 8 | 8 | 1,2 | - New | 21,72 € |
| STRIP8-40-1000 | 1000 | 40 | 50 | 13 | 13 | 2 | ✓ | 26,35 € |
| STRIP8-60-1000 | 1000 | 60 | 50 | 13 | 13 | 2 | ✓ | 32,43 € |
| STRIP8-80-1000 | 1000 | 80 | 50 | 13 | 13 | 2 | ✓ | 36,71 € |
| STRIP8-120-1000 | 1000 | 120 | 50 | 13 | 13 | 2 | - New | 68,22 € |
| STRIP8-150-1000 | 1000 | 150 | 50 | 13 | 13 | 2 | - New | 78,81 € |

*Depending on availability - Dimensions in mm

Sealing brush strip



STRIP

Rigid support

- Provides a seal to the bottoms of doors, gates or roller shutters
- Prevents rodent entry
- Materials:



Frame: anodised aluminium

Brush: black polypropylene fibres



Aluminium
STRIP

Can be modified
to order



DISCOUNTS

| Qty | 1+ | 4+ | 6+ | 10+ |
|-------|------|------|------|------------|
| Disc. | List | -10% | -15% | On request |

| Part number | Length L (mm) | A | B | C | H | S | Stock* | Price each 1 to 3 |
|-------------|---------------|----|------|----|----|----|--------|-------------------|
| STRIP5-25 | 3000 | 17 | 8,0 | 8 | 25 | 25 | ✓ | 50,41 € |
| STRIP8-80 | 3000 | 37 | 12,6 | 13 | 50 | 80 | ✓ | 110,27 € |

*Depending on availability - Dimensions in mm



Sealing brush strip


Right angled rigid support

STRIP

- Provides a seal for the bottoms of doors, gates or roller shutters
- Prevents rodent entry
- Material:
 - Frame: anodised aluminium
 - Brush: black polypropylene fibres with anti-UV treatment

Option

- Can be modified to order (subject to min quantity)



Can be modified to order

DISCOUNTS

| | | | | |
|-------|------|------|------|------------|
| Qty | 1+ | 6+ | 25+ | 50+ |
| Disc. | List | -10% | -15% | On request |

| Part number | Length (mm) | FH | H | B | C | E | Stock* | Price each 1 to 5 |
|-----------------|-------------|----|----|-----|-----|-----|--------|-------------------|
| STRIP3-15F-1000 | 1000 | 15 | 15 | 6,5 | 6,5 | 1,2 | ✓ | 13,77 € |
| STRIP3-20F-1000 | 1000 | 20 | 15 | 6,5 | 6,5 | 1,2 | ✓ | 14,83 € |
| STRIP5-25F-1000 | 1000 | 25 | 25 | 8 | 8 | 1,2 | ✓ | 16,77 € |
| STRIP5-30F-1000 | 1000 | 30 | 25 | 8 | 8 | 1,2 | ✓ | 17,36 € |
| STRIP8-40F-1000 | 1000 | 40 | 50 | 13 | 13 | 2 | ✓ | 26,35 € |
| STRIP8-60F-1000 | 1000 | 60 | 50 | 13 | 13 | 2 | ✓ | 32,43 € |
| STRIP8-80F-1000 | 1000 | 80 | 50 | 13 | 13 | 2 | ✓ | 36,71 € |

*Depending on availability - Dimensions in mm


Our other products



NIN
Self-locking nut, Steel



M1
Worm and wheel set,
Bronze




MR_MMR
Metric section rack,
Steel



PSPD18
Flexible tube handle,
Black PVC




LVT
Miniature motorised
actuator 1A, 1 amp



EZY
Cylindrical stop, Steel



PO
Pull handle - Multi-
sector, Tapped
recessed insert



RPP8
RPP heavy duty
timing belt, RPP8



RPCplss
Swivel castor with
double brake,
Stainless steel -



RDE-N
Sealing washer
Hygienic Usit®,
Stainless steel - Black



PCLA_T
Technopolymer
clamping lever - male,
Plastic



BABreglable
Adjustable ball pin
hardened stainless
steel, adjustable

Complementary products



STRIPF
Sealing brush strip,
1m length



STRIP
Sealing brush strip,
3m length