

Blue EPDM sealing washer

Hygienic Usit®

RDE-BHUSS

- Sealing washer for Hygienic Usit® screws
- Flat metal gasket with elastomer bead for cavity-free, static sealing of screwed connections.
- Material:
 - Stainless steel 1.4404 (316L)
 - Rubber seal: 75 Fluoroprene XP 45, blue

Advantages

- The sealing washer ensures there is no risk of any cavities within a screwed connection.
- Residues or cleaning liquids cannot settle unnoticed thus avoiding any contamination by germs or bacteria.

Use.

- Even if, when tightening the screw connection, the elastomer bead cannot be overloaded by the integrated stainless-steel washer, any material will arrive sooner or later at the end of useable life. Fragments could then be found in foodstuffs.
- The sealing materials used and the colours used make it easy to detect these unwanted elements.


Applications

- For special requirements, such as very greasy and corrosive liquids or very high temperatures, which can occur for example, during cleaning operations.



Warning

- The Hygienic Usit washer cannot guarantee a cavity-free watertight screwed connection unless it is used with screws or nuts from the Hygienic Usit® range.

For hostile environments



Cavity free seal



REMISES

Qty	1+	5+	10+	25+
Disc	Net	-5%	-10%	On request

Part N°	ØD	ØD1	S	For hexagonal nut	Price each
					1 to 4
RDE-4B/HUSS	4,2	9,7	1	M3/M4	10,55 €
RDE-5B/HUSS	5,2	10,7	1	M5	10,42 €
RDE-6B/HUSS	6,2	13,1	1	M6	10,95 €
RDE-8B/HUSS	8,2	16,9	1	M8	14,00 €
RDE-10B/HUSS	10,2	21,2	1,5	M10	16,21 €
RDE-12B/HUSS	12,2	25,5	1,5	M12	16,80 €
RDE-16B/HUSS	16,2	33,9	1,5	M16	25,50 €

All dimensions in mm

0 825 88 6000

Service 0,15 € / min
+ prix appel

Fax

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

39

Our other products



LACT_SS
Stainless steel cam
lever, Male



DB
Bevel gear - Steel
60C40, 2:1



BPFL
Flange bearing, Sheet
steel



PCS625S
Chain sprocket -
Stainless steel,
15.875mm (DIN
08B-1)




MEB-ALI
Moulded plastic bevel
gear (blue nylon), 1:1



WBGV
Lifting ring, Threaded



CFCL
Cam follower,
Lubricating unit



BCM_MPBT
Modular cylindrical
brush, PBT polyester
bristles



INS150
Self tapping insert,
With collar- coarse
thread



PPD
Indexing pin, For
sheet metal



T5P_T10P
Connecting plate, T10



CAP882
Flexible plate chain,
Large range 882

Complementary products



BCTB
Mushroom headed
button Hygienic
Usit®, With male
thread with low head



BCTH
Mushroom headed
button Hygienic
Usit®, With female
thread and high head



BCFH
Mushroom headed
button Hygienic
Usit®, With male
thread and high head



CLAT
Clamping lever
Hygienic Usit®,
Stainless steel