



Support rod for heavy loads


Max load 90,000 N

TCL

- Threaded levelling stem, suitable for heavy loads
- Hollowed stem
- Fine pitch thread allows accurate levelling
- Material:
Chromed steel

Applications

- Machine tools, assembly machines, automated lines



DISCOUNTS

| | | | | |
|-------|------|-----|------|------------|
| Qty | 1+ | 6+ | 10+ | 15+ |
| Disc. | List | -5% | -10% | On request |

| Part number | ØD | ØD1 | SW | ØF | H | Static | Price each |
|--------------|-------|-----|----|----|-----|----------|------------|
| | | | | | | load (N) | 1 to 5 |
| TCL-M30C-110 | M30x2 | 27 | 24 | 17 | 110 | 70000 | 18,92 € |
| TCL-M36C-110 | M36x2 | 33 | 27 | 17 | 110 | 90000 | 20,71 € |

Dimensions in mm

Adjusting nut


Fine thread

ECL

- Adjusting nut
- Fine thread
- Fine pitch thread allows accurate levelling
- Material:
Chromed steel

Applications

- Machine tools, assembly machines, automated lines



DISCOUNTS

| | | | | |
|-------|------|-----|------|------------|
| Qty | 1+ | 6+ | 10+ | 15+ |
| Disc. | List | -5% | -10% | On request |

| Part number | ØD | SW | H | Price each |
|-------------|-------|----|----|------------|
| | | | | 1 to 5 |
| ECL-M24C | M24x2 | 36 | 18 | 2,16 € |
| ECL-M27C | M27x2 | 41 | 12 | 4,07 € |
| ECL-M30C | M30x2 | 36 | 11 | 5,58 € |
| ECL-M35C | M35x2 | 55 | 15 | 8,92 € |
| ECL-M36C | M36x2 | 55 | 15 | 8,92 € |
| ECL-M36C3 | M36x3 | 55 | 15 | 8,92 € |
| ECL-M42C | M42x2 | 65 | 20 | 16,16 € |

Dimensions in mm

Our other products



COA-COG

Surface mounting plate, Surface mounting plate for ball joint



RDS

Safety washer Hygienic Usit®, Stainless steel




ACM_AZ

Mounting bracket for bonnet fastener, Hook



PR105

Articulated foot Ø103, Ø 103



GPLac

Brush, steel



BEF

Bearing housing for miniature ballscrew, Bearing housing



PP35

Worm and wheel gear reducer, from 2.20 to 4.10 Nm



MAX22

Motor-gearbox 12V and 24V DC, from 0,07 to 0,2Nm



PSG25S

Spur gear - precision rolling, Stainless steel



RTE

Rotex®, jaw coupling, steel



PRF_FIX_ANG

Fastener for aluminium profile,



EMS

Stainless steel knurled thumb nut, Knurled

Complementary products



TCL-ECL

Adjusting nut, Fine thread