

White EPDM sealing washer

RDE-WHUSS

Hygienic Usit®

- Sealing washer for Hygienic Usit® screws
- Flat metal gasket with elastomer bead for cavity-free, static sealing of screwed connections.
- Material:
 - Stainless steel 1.4404 (316L)
 - Rubber seal: 70 EPDM 291, white

For use in medical and pharmaceutical industries

Advantages

- The sealing washer ensures there is no risk of any cavities within a screwed connection.
- Residues or cleaning liquids cannot settle unnoticed thus avoiding any contamination by germs or bacteria.

Use.




- Even if, when tightening the screw connection, the elastomer bead cannot be overloaded by the integrated stainless-steel washer, any material will arrive sooner or later at the end of useable life. Fragments could then be found in foodstuffs. The sealing materials used and the colours used make it easy to detect these unwanted elements.

Application

- Mainly used in medical and pharmaceutical industries

Warning

- The Hygienic Usit washer cannot guarantee a cavity-free watertight screwed connection unless it is used with screws or nuts from the Hygienic Usit® range.



REMISES

Qty	1+	5+	10+	25+
Disc	Net	-5%	-10%	On request

Part N°	ØD	ØD1	S	For hexagonal nut	Price each
					1 to 4
RDE-4W/HUSS	4,2	9,7	1	M3/M4	6,56 €
RDE-5W/HUSS	5,2	10,7	1	M5	6,47 €
RDE-6W/HUSS	6,2	13,1	1	M6	6,79 €
RDE-8W/HUSS	8,2	16,9	1	M8	8,67 €
RDE-10W/HUSS	10,2	21,2	1,5	M10	10,07 €
RDE-12W/HUSS	12,2	25,5	1,5	M12	10,42 €
RDE-16W/HUSS	16,2	33,9	1,5	M16	15,82 €

All dimensions in mm

Our other products



PNA

PERIFLEX elastic coupling, Complete coupling



DOMI120

DOMILINE - Accessories, Plate



KB_WW

Linear bearing, Economy range




RIMtce

Locking castor, with central hole



PRF_BASE

Floor anchor, Base plate



P30

Worm and wheel gearbox, up to 8.80 Nm



TB_ECO

Bevel gear - Steel C43, 3:1



RFK48C

Hypoid gearbox - Stainless steel, up to 350 Nm




NSKB

Drylin® N miniature guidance, Rail end cap



RFV40

Worm and wheel gearbox - Stainless steel, up to 47 Nm



M2

Wheel, Bronze



CHMX_CHMDX

Worm and wheel gearbox, CHMR and CHM gearboxes single sided output shaft

Complementary products



VHEM

Hexagonal headed bolt with collar Hygienic Usit®, Stainless steel



CLAT

Clamping lever Hygienic Usit®, Stainless steel



PGMhuss

Carrying handle Hygienic Usit®, Stainless steel



EBE

Cap nut Hygienic Design®, With collar