

- **Conforms to DIN 975**
- **Material:**
Stainless steel: 303/304 - A2
- **Working temperature up to +430°C**

Uses


- Suitable for harsh environments

Options

- Stainless steel 316

Accessories

- Nuts **SHN** (tome 1 p.569)
- Stainless steel screws
- **MCL** and **MHX** sleeves (tome 1 p.524-528)



DISCOUNTS

| | | | | |
|--------------|------|------|------|------------|
| Qty | 1+ | 6+ | 20+ | 40+ |
| Disc. | List | -15% | -20% | On request |

| Part number | Thread | Pitch | Length (mm) | Stock* | Price each 1 to 5 |
|----------------|--------|-------|-------------|--------|-------------------|
| TIF2-1000/SS | M2 | 0,40 | 1000 | ✓ | 11,26 € |
| TIF2.5-1000/SS | M2,5 | 0,45 | 1000 | - | 12,35 € |
| TIF3-1000/SS | M3 | 0,50 | 1000 | ✓ | 6,70 € |
| TIF4-1000/SS | M4 | 0,70 | 1000 | ✓ | 4,44 € |
| TIF5-1000/SS | M5 | 0,80 | 1000 | ✓ | 3,06 € |
| TIF6-1000/SS | M6 | 1,00 | 1000 | ✓ | 3,38 € |
| TIF8-1000/SS | M8 | 1,25 | 1000 | ✓ | 6,40 € |
| TIF10-1000/SS | M10 | 1,50 | 1000 | ✓ | 10,26 € |
| TIF12-1000/SS | M12 | 1,75 | 1000 | ✓ | 14,86 € |
| TIF14-1000/SS | M14 | 2,00 | 1000 | ✓ | 20,44 € |
| TIF16-1000/SS | M16 | 2,00 | 1000 | ✓ | 24,85 € |
| TIF18-1000/SS | M18 | 2,50 | 1000 | - | 36,37 € |
| TIF20-1000/SS | M20 | 2,50 | 1000 | ✓ | 40,50 € |
| TIF22-1000/SS | M22 | 2,50 | 1000 | - | 53,80 € |
| TIF24-1000/SS | M24 | 3,00 | 1000 | - | 57,99 € |
| TIF27-1000/SS | M27 | 3,00 | 1000 | - | 88,19 € |
| TIF30-1000/SS | M30 | 3,50 | 1000 | - | 111,53 € |
| TIF33-1000/SS | M33 | 3,50 | 1000 | - | On request |
| TIF36-1000/SS | M36 | 4,00 | 1000 | - | 150,75 € |

* Depending on availability - Dimensions in mm

Threaded stud **DIN 976A**




TIF

Steel

- Short threaded stud

- Material:

Galvanised steel, class 4.6



Info.


- Other lengths available on request

Accessories

- SHN nuts (tome 1 p.569)

- MCL and MHX sleeves

(tome 1 p.524-528)



DISCOUNTS

| | | | |
|-------|----------|------------|-----|
| Qty | 1+ | 5+ | 15+ |
| Disc. | List -5% | On request | |


| Part number | ØF | L | Quantity per pack | Price each 1 to 4 |
|-------------|-----|-----|-------------------|-------------------|
| TIF6-30/B | M6 | 30 | 200 | 26,73 € |
| TIF6-40/B | M6 | 40 | 200 | 32,16 € |
| TIF6-50/B | M6 | 50 | 200 | 36,56 € |
| TIF6-60/B | M6 | 60 | 200 | 47,48 € |
| TIF6-70/B | M6 | 70 | 200 | 51,88 € |
| TIF6-80/B | M6 | 80 | 200 | 55,20 € |
| TIF6-100/B | M6 | 100 | 200 | 68,31 € |
| TIF6-120/B | M6 | 120 | 200 | 79,26 € |
| TIF8-30/B | M8 | 30 | 200 | 36,56 € |
| TIF8-40/B | M8 | 40 | 200 | 44,25 € |
| TIF8-50/B | M8 | 50 | 200 | 49,68 € |
| TIF8-60/B | M8 | 60 | 200 | 60,63 € |
| TIF8-70/B | M8 | 70 | 200 | 66,15 € |
| TIF8-80/B | M8 | 80 | 200 | 72,70 € |
| TIF8-100/B | M8 | 100 | 200 | 83,67 € |
| TIF8-120/B | M8 | 120 | 200 | 149,94 € |
| TIF8-140/B | M8 | 140 | 200 | 140,56 € |
| TIF10-30/B | M10 | 30 | 100 | 29,21 € |
| TIF10-40/B | M10 | 40 | 100 | 31,95 € |
| TIF10-50/B | M10 | 50 | 100 | 35,24 € |
| TIF10-60/B | M10 | 60 | 100 | 41,83 € |
| TIF10-70/B | M10 | 70 | 100 | 51,08 € |
| TIF10-80/B | M10 | 80 | 100 | 58,81 € |
| TIF10-100/B | M10 | 100 | 100 | 66,96 € |
| TIF10-120/B | M10 | 120 | 100 | 88,85 € |
| TIF10-140/B | M10 | 140 | 100 | 100,89 € |
| TIF10-160/B | M10 | 160 | 100 | 115,12 € |
| TIF12-40/B | M12 | 40 | 100 | 40,71 € |
| TIF12-50/B | M12 | 50 | 100 | 48,37 € |
| TIF12-60/B | M12 | 60 | 100 | 57,65 € |
| TIF12-70/B | M12 | 70 | 100 | 68,07 € |
| TIF12-80/B | M12 | 80 | 100 | 80,13 € |
| TIF12-100/B | M12 | 100 | 100 | 94,34 € |
| TIF12-120/B | M12 | 120 | 100 | 127,16 € |
| TIF12-140/B | M12 | 140 | 100 | 146,30 € |
| TIF12-160/B | M12 | 160 | 100 | 167,66 € |

Dimensions in mm

- Short threaded stud

- Material:

Stainless steel, 304



DISCOUNTS

| | | | |
|-------|----------|------------|-----|
| Qty | 1+ | 5+ | 15+ |
| Disc. | List -5% | On request | |

| Part number | ØF | L | Quantity per pack | Price each 1 to 4 |
|----------------|-----|-----|-------------------|-------------------|
| TIF6-30/SS/B | M6 | 30 | 100 | 56,82 € |
| TIF6-40/SS/B | M6 | 40 | 100 | 58,20 € |
| TIF6-50/SS/B | M6 | 50 | 100 | 63,15 € |
| TIF6-60/SS/B | M6 | 60 | 100 | 69,96 € |
| TIF6-70/SS/B | M6 | 70 | 100 | 77,23 € |
| TIF6-80/SS/B | M6 | 80 | 100 | 83,56 € |
| TIF6-100/SS/B | M6 | 100 | 100 | 97,16 € |
| TIF6-120/SS/B | M6 | 120 | 100 | 110,76 € |
| TIF8-30/SS/B | M8 | 30 | 100 | 59,54 € |
| TIF8-40/SS/B | M8 | 40 | 100 | 69,96 € |
| TIF8-50/SS/B | M8 | 50 | 100 | 80,85 € |
| TIF8-60/SS/B | M8 | 60 | 100 | 96,71 € |
| TIF8-70/SS/B | M8 | 70 | 100 | 112,10 € |
| TIF8-80/SS/B | M8 | 80 | 100 | 127,52 € |
| TIF8-100/SS/B | M8 | 100 | 100 | 140,20 € |
| TIF8-120/SS/B | M8 | 120 | 100 | 155,62 € |
| TIF8-140/SS/B | M8 | 140 | 100 | 177,81 € |
| TIF10-30/SS/B | M10 | 30 | 100 | 84,91 € |
| TIF10-40/SS/B | M10 | 40 | 100 | 102,60 € |
| TIF10-50/SS/B | M10 | 50 | 100 | 120,26 € |
| TIF10-60/SS/B | M10 | 60 | 100 | 136,58 € |
| TIF10-70/SS/B | M10 | 70 | 100 | 149,27 € |
| TIF10-80/SS/B | M10 | 80 | 100 | 164,67 € |
| TIF10-100/SS/B | M10 | 100 | 100 | 195,94 € |
| TIF10-120/SS/B | M10 | 120 | 100 | 227,67 € |
| TIF10-140/SS/B | M10 | 140 | 100 | 263,03 € |
| TIF10-160/SS/B | M10 | 160 | 100 | 299,29 € |
| TIF12-40/SS/B | M12 | 40 | 100 | 156,51 € |
| TIF12-50/SS/B | M12 | 50 | 100 | 190,04 € |
| TIF12-60/SS/B | M12 | 60 | 100 | 218,16 € |
| TIF12-80/SS/B | M12 | 80 | 100 | 276,61 € |
| TIF12-100/SS/B | M12 | 100 | 100 | 331,44 € |
| TIF12-120/SS/B | M12 | 120 | 100 | 389,02 € |
| TIF12-140/SS/B | M12 | 140 | 100 | 447,45 € |
| TIF12-160/SS/B | M12 | 160 | 100 | 518,60 € |

Dimensions in mm