

White EPDM sealing washer

RDE-WHUSS

Hygienic Usit®

- Sealing washer for Hygienic Usit® screws
- Flat metal gasket with elastomer bead for cavity-free, static sealing of screwed connections.
- Material:
 - Stainless steel 1.4404 (316L)
 - Rubber seal: 70 EPDM 291, white

For use in medical and pharmaceutical industries

Advantages

- The sealing washer ensures there is no risk of any cavities within a screwed connection.
- Residues or cleaning liquids cannot settle unnoticed thus avoiding any contamination by germs or bacteria.

Use.




- Even if, when tightening the screw connection, the elastomer bead cannot be overloaded by the integrated stainless-steel washer, any material will arrive sooner or later at the end of useable life. Fragments could then be found in foodstuffs. The sealing materials used and the colours used make it easy to detect these unwanted elements.

Application

- Mainly used in medical and pharmaceutical industries

Warning

- The Hygienic Usit washer cannot guarantee a cavity-free watertight screwed connection unless it is used with screws or nuts from the Hygienic Usit® range.



REMISES

Qty	1+	5+	10+	25+
Disc	Net	-5%	-10%	On request

Part N°	ØD	ØD1	S	For hexagonal nut	Price each
					1 to 4
RDE-4W/HUSS	4,2	9,7	1	M3/M4	6,56 €
RDE-5W/HUSS	5,2	10,7	1	M5	6,47 €
RDE-6W/HUSS	6,2	13,1	1	M6	6,79 €
RDE-8W/HUSS	8,2	16,9	1	M8	8,67 €
RDE-10W/HUSS	10,2	21,2	1,5	M10	10,07 €
RDE-12W/HUSS	12,2	25,5	1,5	M12	10,42 €
RDE-16W/HUSS	16,2	33,9	1,5	M16	15,82 €

All dimensions in mm

Our other products



CHMR50

Worm and wheel gear reducer, up to 107 Nm



E20

Right angle helical reducers, from 0.60 to 3.84 Nm



SH1

Parallel axis helical gear, Steel 20NCD2



HRV

V-rail guidance Simple Select® system, Rail with carriage



CHA1056-UPA

Molded polyamide face-mounted hinge, Black polyamide



712_001

Ball knob, spherical



PTA100

Articulated levelling foot, pressed base Ø100, Ø 100



MACss

Stainless steel carabiner, Stainless steel



WJUM10

Drylin® W bearing block, Slide



PPCcss

Pad eye on mounting plate squarred,



SSDB

Stainless steel bevel gear, 2:1



SUA4_L

Chain link, Steel

Complementary products



CLAT

Clamping lever Hygienic Usit® - male, Stainless steel



PGMhuss

Pull handle Hygienic Usit®, Stainless steel



BCTH

Mushroom headed button Hygienic Usit®, With female thread and high ...



VPR

Wing screw Hygienic Usit®, Stainless steel