

Polyamide castor with central hole


For heavy loads up to 600kg

RPCTC

- Industrial wheel suitable for loads up to 600kg
- Swivel system uses two ball races
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Smooth central bore
- Materials:
 - Top plate: pressed steel sheet, protected by bright zinc plating
 - Polyamide wheel (see RPC)
 - Working temperature range: - 30°C to + 80°C

Advantages

- Light
- Will not mark or stain floor
- Low rolling resistance
- For solid, hard floors



DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	ØE	Swivel interference ØK	Max load (kg)	Price each 1 to 9
Swivel							
RPC60/TC/P	60	31	97	12	140	200	8,74 €
RPC80/TC/P	80	32	106	12	160	250	9,28 €
RPC100/TC/P	100	32	124	12	184	300	9,72 €
RPC125/TC/P	125	36	152	12	210	350	14,47 €
RPC150/TC/P	150	37	181	12	246	400	20,32 €
RPC160/TC/P	160	40	189	12,5	268	500	41,09 €
RPC200/TC/P	200	50	232	12,5	318	600	47,24 €
Swivel with double brake							
RPC80/TC/PDB	80	32	106	12	290	250	14,64 €
RPC100/TC/PDB	100	32	124	12	290	300	15,37 €
RPC125/TC/PDB	125	36	152	12	290	350	19,53 €
RPC150/TC/PDB	150	37	181	12	290	400	25,66 €
RPC160/TC/PDB	160	40	189	12,5	268	500	51,83 €
RPC200/TC/PDB	200	50	232	12,5	318	600	53,78 €

Dimensions in mm

0 825 88 6000
 Service 0,15 € / min
 + prix appel

Fax

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

267

Our other products



PO

Pull handle - Multi-sector, Tapped recessed insert



RCC_RCX

Spherical tilt washer - DIN6319, convex



UCP_SS

Stainless steel pillow block bearing, Stainless steel



DPAR_DKON

Progressive stop, Steel



NCT_AT

Variable angle connector, Variable angle



M0

Worm and wheel set, Bronze



RVM25

Manually operated gearbox, Bevel



VPRA_M

Handwheel with handle, Thermosetting plastic - stainless steel hub



WS16

Drylin® W rail, Rail



BOX-WM

Box set of washer - DIN125, Box set of



BLHB30

Right angled gearbox, bored shafts, up to



MAC

Carabiner DIN5299 steel, Steel

Complementary products




RPCtcss

Swivel castor with central hole, Stainless steel - Polyamide



TSRTC

Stem support for castor, For swivel castor with central hole



RPC

Wheel, Polyamide



RPCtc

Swivel castor with central hole, Steel - Polyamide - with double brake