

# Polyamide castor with central hole


For heavy loads up to 600kg

RPC<sub>TC</sub>

- Industrial wheel suitable for loads up to 600kg
- Swivel system uses two ball races
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Smooth central bore
- Materials:
  - Top plate: pressed steel sheet, protected by bright zinc plating
  - Polyamide wheel (see RPC)
  - Working temperature range: - 30°C to + 80°C

## Advantages

- Light
- Will not mark or stain floor
- Low rolling resistance
- For solid, hard floors



## DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	ØE	Swivel interference ØK	Max load (kg)	Price each 1 to 9
<b>Swivel</b>							
RPC60/TC/P	60	31	97	12	140	200	8,74 €
RPC80/TC/P	80	32	106	12	160	250	9,28 €
RPC100/TC/P	100	32	124	12	184	300	9,72 €
RPC125/TC/P	125	36	152	12	210	350	14,47 €
RPC150/TC/P	150	37	181	12	246	400	20,32 €
RPC160/TC/P	160	40	189	12,5	268	500	41,09 €
RPC200/TC/P	200	50	232	12,5	318	600	47,24 €
<b>Swivel with double brake</b>							
RPC80/TC/PDB	80	32	106	12	290	250	14,64 €
RPC100/TC/PDB	100	32	124	12	290	300	15,37 €
RPC125/TC/PDB	125	36	152	12	290	350	19,53 €
RPC150/TC/PDB	150	37	181	12	290	400	25,66 €
RPC160/TC/PDB	160	40	189	12,5	268	500	51,83 €
RPC200/TC/PDB	200	50	232	12,5	318	600	53,78 €

Dimensions in mm

**0 825 88 6000**  
 Service 0,15 € / min  
 + prix appel

Fax

cial2@hpceurope.com

**HPC**

SUPPLEMENT 2019

267

## Our other products



RPB

Ball screw bearing unit, Support



HTD8M\_30

HTD Heavy duty timing pulley, HTD8 Steel



PRF4590

Standard aluminium profile, 45 x 90 mm




PLA

Flat magnet, Flat magnet



PSG125

Spur gear - precision range, Case hardened steel 20NCD2



QNUP

Single row cylindrical roller bearing, 1 fixed inner flange and 1 fr...



DIV

Locking bolt, With grip - Steel



DOMI50

Accessories, Plate



CHML40

Worm and wheel gear reducer, up to 57 Nm - Integrated torque limiter



STL

Guidance brush - Rail, Rail



DFG

Flat suction cup, silicon



HRV

V-rail guidance Simple Select® system, Rail with carriage

## Complementary products



TSRTC

Stem support for caster, For swivel caster with central hole



RPC

Wheel, Polyamide



RBNtc

Swivel caster with central hole, Steel - rubber



RBGtc

Swivel caster with central hole, Steel - grey rubber - with double b...