

Free running wheel with central hole

RURT

For loads up to 350kg

- Light industrial castor for loads up to 350kg
- Materials:
 - Top bracket/plate: Plated steel sheet
 - Polyurethane covered wheel, 85 Shore
 - Aluminium rim
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Hub with ball bearing
- Working temperature range: -30 to +80°C

swivel

For rough floors




Advantages

- Smooth and quiet running
- Resists wear
- Very strong
- Recommended for its exceptional resistance and its long-term service
- Low risk of flat spots developing if the wheel is not used

Applications

- Rough floors
- Can be used where metal chips, solvents, oil or grease is present



DISCOUNTS

Qty	1+	10+	30+
Disc. List	-5%	On request	

Part number	ØD	H	B	A	F	E	Swivel interference ØK	Max load (kg)	Price each 1 to 9
Swivel									
RURT80/P	80	106	40	12	41	12	162	180	26,07 €
RURT100/P	100	126	40	12	41	12	184	220	28,42 €
RURT125/P	125	153	40	15	41	12	216	260	32,30 €
RURT150/P	150	180	40	20	50	12	244	350	32,30 €
Swivel with double brake									
RURT80/PDB	80	106	40	12	41	12	290	180	31,19 €
RURT100/PDB	100	126	40	12	41	12	290	220	33,83 €
RURT125/PDB	125	153	40	15	41	12	290	260	37,65 €
RURT150/PDB	150	180	40	20	50	12	290	350	50,18 €

Dimensions in mm

Our other products



CLM
Male clevis end,
Stainless steel short



Gal-cardan
Single universal joint
eco series, Low duty



RVM25
Manually operated
gearbox, Bevel



HLA24
Right angle spiro
bevel gearbox, Up to
78Nm



BOX-TOR-G
Box set of Nitrile O-
rings in nitrile, 3.00 x
1.50mm to 30.20 x
3.00



RBNpl
Swivel castor with
plate, Steel - rubber




WING
Manually tightened
wing nut, Steel (ANSI
B18-17)



DZY
Cylindrical stop, Steel



DOMI120
Domino 120
adjustable slide, Slide



PRF4545r90
Standard aluminium
profile, 45 x 45 mm -



BOX-TOR-MAX
Box set of Nitrile O-
rings in nitrile, 2.90 x



DOMI120
Accessories, Plate

Complementary products



RUR
Wheel, Polyurethane -
Aluminium rim (Free
running)



TSRTC
Stem support for
castor, For swivel
castor with central
hole



RUR
Swivel castor with
central hole,
Polyurethane -
Aluminium rim (Free
running)

...



RURp
Fixed castor with
plate, Polyurethane -
Aluminium rim (Free
running)