

Stainless steel ball bearing ABEC 1


S2RS

With sealed joints

- **Radial contact ball bearing**
- Bearing with 2 sealed joints (2RS)
- **Material:**
Cage + balls: stainless steel AISI 440C
Joint: Neoprene
- **Static and dynamic loads :** these bearings can handle approx 70% of the same loads that an equivalent steel bearing will accept
- **Max. working temperature:** +80°C

Accessories

- Nut FU-SS



DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List	-10%	-15%	-20%	On request

Part number	ØA	ØD	E	Stock*	Price each 1 to 5
S6000-2RS	10	26	8	✓	7,40 €
S6200-2RS	10	30	9	✓	9,30 €
S6001-2RS	12	28	8	✓	8,56 €
S6201-2RS	12	32	10	✓	10,40 €
S6301-2RS	12	37	12	-	14,93 €
S6002-2RS	15	32	9	✓	10,34 €
S6202-2RS	15	35	11	✓	12,42 €
S6302-2RS	15	42	13	-	21,11 €
S6003-2RS	17	35	10	-	15,91 €
S6203-2RS	17	40	12	-	17,31 €
S6303-2RS	17	47	14	-	25,21 €
S6004-2RS	20	42	12	✓	17,99 €
S6204-2RS	20	47	14	-	19,95 €
S6304-2RS	20	52	15	-	27,17 €
S6005-2RS	25	47	12	✓	24,35 €
S6205-2RS	25	52	15	-	29,13 €
S6305-2RS	25	62	17	-	45,04 €
S6006-2RS	30	55	13	✓	30,96 €
S6306-2RS	30	72	19	-	63,89 €
S6007-2RS	35	62	14	-	38,92 €
S6207-2RS	35	72	17	-	57,28 €
S6208-2RS	40	80	18	-	76,31 €

*Depending on availability - Dimensions in mm

Our other products



SBF

Sealed flange bearing unit for Food Industry, cover



AT10-BAR

AT type tooth bar stock, AT10



HRV

V- rail guidance Simple Select® system, Rail with carriage



MDB_MTB

Moulded plastic bevel gear (nylon), 2:1



SRG

Adjustable latch clamp with strike plate, Stroke from 117,4mm to 128mm



PRF-SCREEN-4

Screen support, Support with 4 axes of rotation



AT5-16ECO

AT type timing pulley, Economy range - AT5 aluminium



GP

Spring loaded toggle latch, With padlock-holder




CHTRP

Single and dual output gearboxes, Up



VRBS

Folding lifting ring for welding, Folding - for



R_RR

Narrow spur rack, Steel



CHAR

Spring hinge, screwed

Complementary products



S_ZZ

Deep groove ball bearing, Stainless steel



SF_ZZ

Deep groove ball bearing, Stainless steel



FUSS

Bearing locknut, Self locking locknut - stainless steel lock washer