



Stainless steel/Polymer flanged bearing

4 mounting points

UCFPBT

- Self aligning bearing with 4 mounting points
- Interchangeable with cast iron units
- Grease applicator supplied
- Working temperature: -35°C to +102°C
- Materials:
 - Bearing: Stainless steel AISI 440C
 - Housing: PBT polymer
 - Grease: suitable for food industry



Colour

- UCF/PBT/G: green
- UCF/PBT/W: white

Accessory

- Protective cover

For the food industry



DISCOUNTS

Qty	1+	10+	26+	51+
Disc.	List	-10%	-20%	On request

Part number	ØD	A	E	G	L	ØS	Z	J	Bi	N	Stock*	Price each
UCF201/PBT/G	12	86	63,5	13,4	27,8	11	36,3	18,0	31,0	12,7	✓	92,35 €
UCF202/PBT/G	15	86	63,5	13,4	27,8	11	36,3	18,0	31,0	12,7	✓	87,89 €
UCF203/PBT/G	17	86	63,5	13,4	27,8	11	36,3	18,0	31,0	12,7	-	82,15 €
UCF204/PBT/W	20	86	63,5	13,4	27,8	11	36,3	18,0	31,0	12,7	✓	21,38 €
UCF205/PBT/W	25	95	70,0	14,0	28,0	11	36,7	17,0	34,0	14,3	✓	27,95 €
UCF206/PBT/W	30	107	83,0	14,3	31,5	11	41,4	19,2	38,1	15,9	✓	40,41 €
UCF207/PBT/W	35	118	92,0	15,5	34,8	13	46,9	21,5	42,9	17,5	-	50,30 €
UCF208/PBT/W	40	130	102,0	17,0	37,5	14	53,2	23,0	49,2	19,0	✓	61,54 €

*Depending on availability - Dimensions in mm

Our other products



BPHF

Ball transfer unit push fit, Heavy



LRR-53

Spring loaded latch, Spring return latch - steel



GAL_20

Conveyor roller for Ø20mm spindle, Self-lubricating polyamide



ZBconique

Machined plastic bevel gear, 1:1



HTD14M_85

HTD Heavy duty timing pulley, HTD14 Cast



M0

Worm and wheel set, Non hardened steel



RT25

Self-centering flanged locking assembly, Medium/high torque



CNA-CNG

Right angled mounting plate, Right angled mounting plate for ball jo...



GP75

Spring loaded toggle latch, Standard



GMK17_RG

Joint for guiding profile, Rounded



GCB880

Curved track for slat top chain, Ranges 880



PW_PWG3

Worm - precision range, Steel

Complementary products



UCP_PBT

Stainless/Polymer pillow block bearing, Polymer and stainless steel




UCFL_PBT

Stainless steel/Polymer flanged bearing, Polymer and stainless steel



BPFss

Pressed stainless steel flange bearing, Stainless steel



UCF_PBT

Stainless steel/Polymer flanged bearing, Polymer and stainless steel