



Stainless steel/Polymer flanged bearing

4 mounting points

UCFPBT

- Self aligning bearing with 4 mounting points
- Interchangeable with cast iron units
- Grease applicator supplied
- Working temperature: -35°C to +102°C
- Materials:
 - Bearing: Stainless steel AISI 440C
 - Housing: PBT polymer
 - Grease: suitable for food industry




Colour

- UCF/PBT/G: green
- UCF/PBT/W: white

Accessory

- Protective cover

For the food industry



DISCOUNTS

Qty	1+	10+	26+	51+
Disc.	List	-10%	-20%	On request

Part number	ØD	A	E	G	L	ØS	Z	J	Bi	N	Stock*	Price each
UCF201/PBT/G	12	86	63,5	13,4	27,8	11	36,3	18,0	31,0	12,7	✓	92,35 €
UCF202/PBT/G	15	86	63,5	13,4	27,8	11	36,3	18,0	31,0	12,7	✓	87,89 €
UCF203/PBT/G	17	86	63,5	13,4	27,8	11	36,3	18,0	31,0	12,7	-	82,15 €
UCF204/PBT/W	20	86	63,5	13,4	27,8	11	36,3	18,0	31,0	12,7	✓	21,38 €
UCF205/PBT/W	25	95	70,0	14,0	28,0	11	36,7	17,0	34,0	14,3	✓	27,95 €
UCF206/PBT/W	30	107	83,0	14,3	31,5	11	41,4	19,2	38,1	15,9	✓	40,41 €
UCF207/PBT/W	35	118	92,0	15,5	34,8	13	46,9	21,5	42,9	17,5	-	50,30 €
UCF208/PBT/W	40	130	102,0	17,0	37,5	14	53,2	23,0	49,2	19,0	✓	61,54 €

*Depending on availability - Dimensions in mm

Our other products



CLLCLLP
Clevis components,
long version, Steel -
long version




BOX-TOR-INCH
Box set of Nitrile O-
rings in inch NBR90Sh
A, For fasteners and
fitt...




RT61
Self-centering locking
Assembly,
Medium/low torque



M0
Worm and wheel set,
Machined plastic
(delrin)



STL
Guidance brush -
Brush, Brush



PPRss
Pad eye on mounting
plate round, Stainless
steel



T10courroie
T type timing belt,
T10 Steel cored
polyurethane



SVT30
Screwjack with
travelling screw, with
translating screw



RBS
Dynamic washer
DIN2093, Steel



BLHB40
Right angled gearbox,
bored shafts, up to



SCR
Suction cup threaded
insert, Adaptor for



DOMI30
Accessories, Fixing kit

Complementary products



UCF_PBT
Stainless
steel/Polymer flanged
bearing, Polymer and
stainless steel



UCP_PBT
Stainless/Polymer
pillow block bearing,
Polymer and stainless
steel



UCFL_PBT
Stainless
steel/Polymer flanged
bearing, Polymer and
stainless steel



SBF
Open flange bearing
unit for food industry,
cover