



Stainless steel/Polymer flanged bearing

4 mounting points

UCFPBT

- Self aligning bearing with 4 mounting points
- Interchangeable with cast iron units
- Grease applicator supplied
- Working temperature: -35°C to +102°C
- Materials:
 - Bearing: Stainless steel AISI 440C
 - Housing: PBT polymer
 - Grease: suitable for food industry




Colour

- UCF/PBT/G: green
- UCF/PBT/W: white

Accessory

- Protective cover

For the food industry



DISCOUNTS

Qty	1+	10+	26+	51+
Disc.	List	-10%	-20%	On request

Part number	ØD	A	E	G	L	ØS	Z	J	Bi	N	Stock*	Price each
UCF201/PBT/G	12	86	63,5	13,4	27,8	11	36,3	18,0	31,0	12,7	✓	92,35 €
UCF202/PBT/G	15	86	63,5	13,4	27,8	11	36,3	18,0	31,0	12,7	✓	87,89 €
UCF203/PBT/G	17	86	63,5	13,4	27,8	11	36,3	18,0	31,0	12,7	-	82,15 €
UCF204/PBT/W	20	86	63,5	13,4	27,8	11	36,3	18,0	31,0	12,7	✓	21,38 €
UCF205/PBT/W	25	95	70,0	14,0	28,0	11	36,7	17,0	34,0	14,3	✓	27,95 €
UCF206/PBT/W	30	107	83,0	14,3	31,5	11	41,4	19,2	38,1	15,9	✓	40,41 €
UCF207/PBT/W	35	118	92,0	15,5	34,8	13	46,9	21,5	42,9	17,5	-	50,30 €
UCF208/PBT/W	40	130	102,0	17,0	37,5	14	53,2	23,0	49,2	19,0	✓	61,54 €

*Depending on availability - Dimensions in mm

Our other products




WSRM

Cylindrical polymer nut, Polymer (Iglidur®) - 1 thread



PM2

Worm and wheel set, Bronze



EPRF

High helix leadscrew, Flanged nut - up to 40mm per rotation



PRF-SRA

Lock for aluminium profile, Lock



CHM50

Worm and wheel gear reducer, up to 107 Nm



AC144

Strike for toggle latch, 22mm



CAP881

Side flexing slim slat top chain stainless steel, Narrow range 881



TBEBASE10

Economic mini-table with trapezoidal leadscrew, 1kg



MCL

Cylindrical threaded sleeve, Cylindrical -



INO

Internal gear, Steel 20NCD2



PTA100ssEB

Articulated foot with sheet metal base



PHT

Pull handle, Up to 250 °C

Complementary products



UCP_PBT

Stainless/Polymer pillow block bearing, Polymer and stainless steel



UCFL_PBT

Stainless steel/Polymer flanged bearing, Polymer and stainless steel



UCF_PBT

Stainless steel/Polymer flanged bearing, Polymer and stainless steel



BPFss

Pressed stainless steel flange bearing, Stainless steel