



# Stainless steel/Polymer flanged bearing

## 4 mounting points

## UCFPBT

- Self aligning bearing with 4 mounting points
- Interchangeable with cast iron units
- Grease applicator supplied
- Working temperature: -35°C to +102°C
- Materials:
  - Bearing: Stainless steel AISI 440C
  - Housing: PBT polymer
  - Grease: suitable for food industry

### Colour



- UCF/PBT/G: green
- UCF/PBT/W: white

### Accessory

- Protective cover



**For the food industry**



### DISCOUNTS

Qty	1+	10+	26+	51+
Disc.	List	-10%	-20%	On request

Part number	ØD	A	E	G	L	ØS	Z	J	Bi	N	Stock*	Price each 1 to 9
UCF201/PBT/G	12	86	63,5	13,4	27,8	11	36,3	18,0	31,0	12,7	✓	92,35 €
UCF202/PBT/G	15	86	63,5	13,4	27,8	11	36,3	18,0	31,0	12,7	✓	87,89 €
UCF203/PBT/G	17	86	63,5	13,4	27,8	11	36,3	18,0	31,0	12,7	-	82,15 €
UCF204/PBT/W	20	86	63,5	13,4	27,8	11	36,3	18,0	31,0	12,7	✓	21,38 €
UCF205/PBT/W	25	95	70,0	14,0	28,0	11	36,7	17,0	34,0	14,3	✓	27,95 €
UCF206/PBT/W	30	107	83,0	14,3	31,5	11	41,4	19,2	38,1	15,9	✓	40,41 €
UCF207/PBT/W	35	118	92,0	15,5	34,8	13	46,9	21,5	42,9	17,5	-	50,30 €
UCF208/PBT/W	40	130	102,0	17,0	37,5	14	53,2	23,0	49,2	19,0	✓	61,54 €

\*Depending on availability - Dimensions in mm

## Our other products



LSM

Trapezoidal rolled leadscrew, Stainless steel - 1 thread



PSG08

Spur gear - precision range, Case hardened steel 20NCD2



PPR

Cylindrical revolving handle, Folding



PSG2DL

Spur gear - precision range, Delrin



HRV

V- rail guidance system, Rail with carriage



ZB

Linear shaft, Hardened ground stainless steel



PPRss

Pad eye on mounting plate, Stainless steel



CHTRP

Single and dual output gearboxes, Up to 9,1 Nm



PTA50

Levelling foot with pressed base, Ø 50



MURP4545

Mini profile-mounted adjusting unit, 45x45mm



CFS

Cam follower, Miniature



PDD

Spring operated plunger with pressure pin, With sensor adaptor

## Complementary products



UCP\_PBT

Pillow block, Polymer and stainless steel



UCFL\_PBT

Flange bearing, Polymer and stainless steel



BPFss

Flange bearing, Stainless steel



UCF\_PBT

Flange bearing, Polymer and stainless steel