

# Stainless/Polymer pillow block bearing

## UCP<sub>PBT</sub>

## 2 mounting points

- Self aligning bearing with 2 mounting points
- Interchangeable with cast iron units
- Grease applicator supplied
- Working temperature: -35°C to +102°C
- Materials:
  - Bearing: Stainless steel AISI 440C
  - Housing: PBT polymer
  - Grease: suitable for food industry





### Colour

- UCP/PBT/G: green
- UCP/PBT/W: white

### Accessory

- Protective cover

**For the food industry**



Typical application

### DISCOUNTS

Qty	1+	10+	26+	25+
Disc.	List	-10%	-20%	On request

Part number	ØD	H	A	E	B	S1	S2	G	W	Bi	N	Stock*	Price each 1 to 9
UCP201/PBT/G	12	33,3	127,0	95	38	11	14	14,2	65,5	31,0	12,7	✓	90,67 €
UCP202/PBT/G	15	33,3	127,0	95	38	11	14	14,2	65,5	31,0	12,7	✓	86,27 €
UCP203/PBT/G	17	33,3	127,0	95	38	11	14	14,2	65,5	31,0	12,7	✓	82,15 €
UCP204/PBT/W	20	33,3	127,0	95	38	11	14	14,2	65,5	31,0	12,7	✓	22,20 €
UCP205/PBT/W	25	36,5	140,5	105	38	11	14	14,2	71,0	34,0	14,3	✓	26,77 €
UCP206/PBT/W	30	42,9	163,0	119	46	14	18	17,8	83,0	38,1	15,9	✓	38,84 €
UCP207/PBT/W	35	47,6	168,0	128	48	14	18	18,0	94,5	42,9	17,5	✓	54,44 €
UCP208/PBT/W	40	49,2	184,0	137	54	14	18	19,5	98,0	49,2	19,0	-	62,76 €

\*Depending on availability - Dimensions in mm

## Our other products




RURp

Fixed castor with plate, Polyurethane - Aluminium rim (Free running)



GE\_C

Spherical bushing, Hard chromium / PTFE



VP

Small 6 lobe threaded handle - male, Duroplast - Steel



BLHT40

Right angled gearbox, from 4 to 10.30 Nm




MSP3815

Masterplate® glueable insert rectangular, rectangular with



SHA\_PT

Handwheel with handle, Polyamide



P30

Worm and wheel gear reducer, up to 8.80 Nm




GE\_ES

Spherical bushing, Steel / steel



BOX-INS-W

Box set of self tapping inserts, Boxed set - For wood



RTN

BoWex® curved tooth gear coupling, Nylon



BH01

Single housed bearing, Bearing fitted with adhesive



VDSQCB

Sliding lock adjustment system, Blocking wedge

## Complementary products



UCF\_PBT

Stainless steel/Polymer flanged bearing, Polymer and stainless steel



UCFL\_PBT

Stainless steel/Polymer flanged bearing, Polymer and stainless steel



BPPss

Pressed stainless steel pillow block, Stainless steel



UCP\_PBT

Stainless/Polymer pillow block bearing, Polymer and stainless steel