

UCP_{PBT}

2 mounting points

- Self aligning bearing with 2 mounting points
- Interchangeable with cast iron units
- Grease applicator supplied
- Working temperature: -35°C to +102°C
- Materials:
 - Bearing: Stainless steel AISI 440C
 - Housing: PBT polymer
 - Grease: suitable for food industry





Colour

- UCP/PBT/G: green
- UCP/PBT/W: white

Accessory

- Protective cover

For the food industry



Typical application

DISCOUNTS

Qty	1+	10+	26+	25+
Disc.	List	-10%	-20%	On request

Part number	ØD	H	A	E	B	S1	S2	G	W	Bi	N	Stock*	Price each 1 to 9
UCP201/PBT/G	12	33,3	127,0	95	38	11	14	14,2	65,5	31,0	12,7	✓	90,67 €
UCP202/PBT/G	15	33,3	127,0	95	38	11	14	14,2	65,5	31,0	12,7	✓	86,27 €
UCP203/PBT/G	17	33,3	127,0	95	38	11	14	14,2	65,5	31,0	12,7	✓	82,15 €
UCP204/PBT/W	20	33,3	127,0	95	38	11	14	14,2	65,5	31,0	12,7	✓	22,20 €
UCP205/PBT/W	25	36,5	140,5	105	38	11	14	14,2	71,0	34,0	14,3	✓	26,77 €
UCP206/PBT/W	30	42,9	163,0	119	46	14	18	17,8	83,0	38,1	15,9	✓	38,84 €
UCP207/PBT/W	35	47,6	168,0	128	48	14	18	18,0	94,5	42,9	17,5	✓	54,44 €
UCP208/PBT/W	40	49,2	184,0	137	54	14	18	19,5	98,0	49,2	19,0	-	62,76 €

*Depending on availability - Dimensions in mm

Our other products



DOMI120

Accessories, Plate



SLB

Indexing plunger,
steel class 5.8



CHAPAMss

Weld-on hinge with
flat end, Stainless
steel or Aluminium



CHM40-MOT

Asynchronous AC
motorgearboxes 0.18
to 0.55kW, 0.18 to
0.55kW




EHD08-3

Internal epicyclic
servo reducers, from
20 to 50 Nm



PTKss

Foot for the food
industry, Stainless
steel - 3-A standard



MBrondelle

Stop washer, Stop
washer MB



CHB

Worm and wheel gear
reducer, up to 73 Nm



TS01_TW01

Drylin® T linear slide,
up to 7000 N



GSI

Stainless steel gas
spring, Stainless steel



VB


Small 6 lobe threaded
handle - female,
Duroplast - Stainless



HTD8M_20

HTD Heavy duty
timing pulley, HTD8
Cast

Complementary products



UCF_PBT

Stainless
steel/Polymer flanged
bearing, Polymer and
stainless steel



UCFL_PBT

Stainless
steel/Polymer flanged
bearing, Polymer and
stainless steel



BPPss

Pressed stainless
steel pillow block,
Stainless steel



UCP_PBT

Stainless/Polymer
pillow block bearing,
Polymer and stainless
steel