

# Positioning sleeve for indexing pin New


## SDC

## For pin Ø4 to Ø12


- Suitable for indexing pins and indexing locks
- Low wear due to hardened cone
- Materials:
  - Hardened and burnished steel
  - Hardened stainless steel

### Accessories

- Compatible with the SDA and SDB locating bolt support bracket (tome 1 p.68-69)
- Compatible with the HPC range of indexing pins.



Application example



### DISCOUNTS

Qty	1+	6+	20+
Disc.	Price -10%	On request	On request

Part number	ØD	ØD3		ØD4		L5			For pin diam	Weight (g)	Price each 1 to 5		
		(+0,1)	ØD2	(-0,05)	L1	L2	L3	L4				(+0,5)	
<b>Steel</b>													
SDC12F-4	M12X1,5	4,2	24	12	10	16	11	5	1,5	4	4	17	9,49 €
SDC12F-5	M12X1,5	5,2	24	12	10	16	11	5	1,5	5	4	16	9,55 €
SDC12F-6	M12X1,5	6,2	24	12	10	16	11	5	1,5	6	4	16	9,55 €
SDC16F-8	M16X1,5	8,2	32	16	12	20	13	7	1,5	8	6	32	11,46 €
SDC16F-10	M16X1,5	10,2	32	16	12	20	13	7	1,5	10	6	33	11,38 €
SDC16F-12	M16X1,5	12,2	32	16	12	20	13	7	1,5	12	6	33	11,46 €
<b>Stainless steel</b>													
SDC12F-4/SS	M12X1,5	4,2	24	12	10	16	11	5	1,5	4	4	17	12,75 €
SDC12F-5/SS	M12X1,5	5,2	24	12	10	16	11	5	1,5	5	4	16	12,75 €
SDC12F-6/SS	M12X1,5	6,2	24	12	10	16	11	5	1,5	6	4	16	12,75 €
SDC16F-8/SS	M16X1,5	8,2	32	16	12	20	13	7	1,5	8	6	32	18,53 €
SDC16F-10/SS	M16X1,5	10,2	32	16	12	20	13	7	1,5	10	6	33	18,53 €
SDC16F-12/SS	M16X1,5	12,2	32	16	12	20	13	7	1,5	12	6	33	18,53 €

Dimensions in mm

## Our other products



UFX

Uneflex® elastic coupling, range



EKONSL

Silicone conical elasto buffer, Female mounting



WJRM

Drylin® W hybrid bearing block, Hybrid bearings



LACM\_SS

Stainless steel cam lever, Female



BSM\_LOK

Long-Lok spring plunger with internal hexagonal socket, LONG-LOK - s...



PF30

Worm and wheel gear reducer, up to 8.80 Nm



SER69K-CLE

Quarter turn latch for the food industry, Stainless steel key



SSDB

Stainless steel bevel gear, 2:1



PRF\_BASE

Base plate for aluminium profile,



BUH77

Motor-gearbox 12V and 24V DC, from 0.1



MCLred

Reducing sleeve female/female,



DILC

Indexing plunger with cam, with cam

## Complementary products



SDCss

Positioning sleeve for indexing pin, For pin Ø4 to Ø12



SDA

Locking bolt support bracket, Mounting holes parallel to locating bolt



SDB

Locking bolt support bracket, Mounting holes at 90° to locating bolt



SLB

Indexing plunger, steel class 5.8