

Stainless/Polymer pillow block bearing

UCP_{PBT}

2 mounting points

- Self aligning bearing with 2 mounting points
- Interchangeable with cast iron units
- Grease applicator supplied
- Working temperature: -35°C to +102°C
- Materials:
 - Bearing: Stainless steel AISI 440C
 - Housing: PBT polymer
 - Grease: suitable for food industry





Colour

- UCP/PBT/G: green
- UCP/PBT/W: white

Accessory

- Protective cover

For the food industry



Typical application

DISCOUNTS

Qty	1+	10+	26+	25+
Disc.	List	-10%	-20%	On request

Part number	ØD	H	A	E	B	S1	S2	G	W	Bi	N	Stock*	Price each 1 to 9
UCP201/PBT/G	12	33,3	127,0	95	38	11	14	14,2	65,5	31,0	12,7	✓	90,67 €
UCP202/PBT/G	15	33,3	127,0	95	38	11	14	14,2	65,5	31,0	12,7	✓	86,27 €
UCP203/PBT/G	17	33,3	127,0	95	38	11	14	14,2	65,5	31,0	12,7	✓	82,15 €
UCP204/PBT/W	20	33,3	127,0	95	38	11	14	14,2	65,5	31,0	12,7	✓	22,20 €
UCP205/PBT/W	25	36,5	140,5	105	38	11	14	14,2	71,0	34,0	14,3	✓	26,77 €
UCP206/PBT/W	30	42,9	163,0	119	46	14	18	17,8	83,0	38,1	15,9	✓	38,84 €
UCP207/PBT/W	35	47,6	168,0	128	48	14	18	18,0	94,5	42,9	17,5	✓	54,44 €
UCP208/PBT/W	40	49,2	184,0	137	54	14	18	19,5	98,0	49,2	19,0	-	62,76 €

*Depending on availability - Dimensions in mm

Our other products



BLHT60
Right angled gearbox,
from 26 to 70 Nm



M0
Worm and wheel set,
Non hardened steel



EKGS
Backlash free
coupling Gerwah®,
from 0.5 to 35Nm




BTCW
Cap for square tube to
be welded, To be
welded



V3RA_PT
3-spoked handwheel
with handle,
Polyamide



SSE
Stainless steel
spherical bearing,
Stainless steel / PTFE



M1
Worm and wheel set,
Bronze



HW_HT
Half-rail guide, Rail




CLB_T
Die cast zinc clamping
lever - male, Zamak



CLR
Straight clevis,
Straight clevis for use




CHV
Mechanical speed
variator, from 0,18 to



B
Steel bevel gear, 1:1

Complementary products



UCF_PBT
Stainless
steel/Polymer flanged
bearing, Polymer and
stainless steel



BPPss
Pressed stainless
steel pillow block,
Stainless steel



UCP_PBT
Stainless/Polymer
pillow block bearing,
Polymer and stainless
steel