

Positioning sleeve for indexing pin New

SDC

For pin Ø4 to Ø12


- Suitable for indexing pins and indexing locks
- Low wear due to hardened cone
- Materials:
 - Hardened and burnished steel
 - Hardened stainless steel

Accessories


- Compatible with the SDA and SDB locating bolt support bracket (tome 1 p.68-69)
- Compatible with the HPC range of indexing pins.



NEW!



Application example



DISCOUNTS

Qty	1+	6+	20+
Disc.	Price -10%	On request	On request


Part number	ØD	ØD3		ØD4		L5			For pin diam	Weight (g)	Price each 1 to 5		
		(+0,1)	ØD2	(-0,05)	L1	L2	L3	L4				(+0,5)	
Steel													
SDC12F-4	M12X1,5	4,2	24	12	10	16	11	5	1,5	4	4	17	9,49 €
SDC12F-5	M12X1,5	5,2	24	12	10	16	11	5	1,5	5	4	16	9,55 €
SDC12F-6	M12X1,5	6,2	24	12	10	16	11	5	1,5	6	4	16	9,55 €
SDC16F-8	M16X1,5	8,2	32	16	12	20	13	7	1,5	8	6	32	11,46 €
SDC16F-10	M16X1,5	10,2	32	16	12	20	13	7	1,5	10	6	33	11,38 €
SDC16F-12	M16X1,5	12,2	32	16	12	20	13	7	1,5	12	6	33	11,46 €
Stainless steel													
SDC12F-4/SS	M12X1,5	4,2	24	12	10	16	11	5	1,5	4	4	17	12,75 €
SDC12F-5/SS	M12X1,5	5,2	24	12	10	16	11	5	1,5	5	4	16	12,75 €
SDC12F-6/SS	M12X1,5	6,2	24	12	10	16	11	5	1,5	6	4	16	12,75 €
SDC16F-8/SS	M16X1,5	8,2	32	16	12	20	13	7	1,5	8	6	32	18,53 €
SDC16F-10/SS	M16X1,5	10,2	32	16	12	20	13	7	1,5	10	6	33	18,53 €
SDC16F-12/SS	M16X1,5	12,2	32	16	12	20	13	7	1,5	12	6	33	18,53 €

Dimensions in mm

Our other products




GLB
Small 6 lobe female handle,
Technopolymer -
Stainless steel



ZR
Plastic rack, Delrin



RFKfp
Stainless steel
gearbox - accessories,
Mounting bracket



KITdog
24V DC motorisation
kit, Worm and wheel



DOMI80
Accessories, Plate



DZYSS
Stainless steel
cylindrical stop,
stainless steel



BLH50
Right angled gearbox,
from 7.70 to 20 Nm



SLB
Indexing plunger,
stainless steel




CHA1056-UPA
Molded polyamide
face-mounted hinge,
Black polyamide



E15
Right angle helical
reducers, from 0.40 to
2.53 Nm



CFF
Female rod ends DIN
ISO12240-4, Steel /
bronze



T5M T10M
T type timing belt per
metre, T10 Steel
cored polyurethane

Complementary products



SDC
Positioning sleeve for
indexing pin, For pin
Ø4 to Ø12



SDA
Locking bolt support
bracket, Mounting
holes parallel to
locating bolt



SDB
Locking bolt support
bracket, Mounting
holes at 90° to
locating bolt



SLB
Indexing plunger,
steel class 5.8