

# 3 spoked handwheel with revolving handle

## V3RAPT

## Polyamide


- **Manual operating element**
- Freely revolving handle for manual operation
- **Materials:**  
Wheel: glass fibre reinforced polyamide  
Hub: galvanised steel

### Options

- Different bore diameters
- Keyways
- See modification info on page 64



### Application

- All types of machines



**New Ø300  
Ø375**

### Bore modifications



### DISCOUNTS

<b>Qty</b>	1+	6+	20+
<b>Disc.</b>	List	-5%	On request

Part number	Ød Pré-bore	ØD	H	C	ØA	E	F	ØK	L	ØG	P	ØN	Stock*	Price each 1 to 5
V3RA-100-PT	4	100	46	20	24	12	24	18	96	21	50	M6	✓	18,94 €
V3RA-125-PT	6	125	51	24	24	12	28	20	101	21	50	M6	✓	21,92 €
V3RA-160-PT	6	160	61	28	32	15	31	30	131	23	70	M8	✓	28,24 €
V3RA-200-PT	6	200	74	32	40	15	40	35	164	26	90	M10	✓	39,20 €
V3RA-250-PT	6	250	83	34	48	17	49	35	173	26	90	M10	-	55,68 €
V3RA-300-PT	6	300	93	36	58	18	53	48	183	26	90	M10	New	88,48 €
V3RA-375-PT	6	375	104	38	58	18	53	48	194	26	90	M10	New	130,25 €

\*Subject to availability - Dimensions in mm

## Our other products




CFES  
Eccentric cam follower, Eccentric



SVG  
Adjustable latch clamp with strike plate, Stroke from 174mm to 190mm



BPO  
Quadro linear ball bearing unit, Included 4 linear ball bearings



M1  
Worm and wheel set, Machined plastic (delrin)



CHAL3  
Piano hinge, Aluminium



PRF\_CLIP\_45  
Cable clip for aluminium profile, For cable chute



GG2  
Ground spur gear, Heat treated steel



NPTR10  
Adjustable cross clamp, Adjustable



JCSs  
Single stainless steel universal joint, Low duty



NT62  
Spur gear coaxial gearbox, from 6 to 18 Nm - In-line




H2  
Crossed helical gear crossed axis at 90°, Steel 20NCD2



DOMI50  
Domino 50 adjustable slide, Slide DOMILINE 50 with counter and handw...

## Complementary products



HLUss  
Spoked handwheel, Stainless steel 316



MHQMEP  
Arm with rotating handle, Square bore



SHA\_PTR  
Handwheel with folding handle, Polyamide



VPRA\_M  
Handwheel with handle, Thermosetting plastic - galvanised steel hub