


- **Dual threaded screw wood/metal**
- Allows a metal object to be fixed to wood
- Materials:
 - Galvanised steel
 - Stainless steel, 304
- Supplied by the pack




Mounting

- Screw should first be inserted into the wood using a suitable spanner
- Compatible with **N, SHN, NINA** and **NIN** nuts



Typical application



DISCOUNTS Steel

Qty	1+	6+	20+	50+
Disc.	List	-10%	-20%	On request

DISCOUNTS S/steel

Qty	1+	6+	10+
Disc.	List	-5%	On request

Part number	Part number		ØF	L	Qty per pack		Price each 1 to 5	
	Steel	Stainless steel			Steel	S/steel	Steel	S/steel
VCMB5-40/B	-	-	M5	40	100	-	5,93 €	-
VCMB5-50/B	-	-	M5	50	100	-	9,82 €	-
VCMB6-60/B	VCMB6-60/SS/B	-	M6	60	100	100	11,55 €	38,18 €
VCMB6-80/B	VCMB6-80/SS/B	-	M6	80	100	100	19,09 €	47,97 €
VCMB6-100/B	VCMB6-100/SS/B	-	M6	100	100	100	31,24 €	64,50 €
VCMB6-120/B	VCMB6-120/SS/B	-	M6	120	100	100	32,36 €	72,65 €
VCMB8-50/B	VCMB8-50/SS/B	-	M8	50	100	100	12,33 €	101,81 €
VCMB8-60/B	VCMB8-60/SS/B	-	M8	60	100	100	13,30 €	59,98 €
VCMB8-80/B	VCMB8-80/SS/B	-	M8	80	100	50	17,50 €	40,17 €
VCMB8-100/B	VCMB8-100/SS/B	-	M8	100	100	50	21,81 €	54,45 €
VCMB8-120/B	VCMB8-120/SS/B	-	M8	120	100	50	26,57 €	63,40 €
VCMB8-140/B	VCMB8-140/SS/B	-	M8	140	100	50	34,36 €	73,72 €
VCMB8-160/B	VCMB8-160/SS/B	-	M8	160	100	50	38,39 €	72,81 €
VCMB10-60/B	-	-	M10	60	100	-	23,42 €	-
VCMB10-80/B	VCMB10-80/SS/B	-	M10	80	50	25	16,18 €	49,07 €
VCMB10-100/B	VCMB10-100/SS/B	-	M10	100	50	25	19,81 €	41,04 €
VCMB10-120/B	VCMB10-120/SS/B	-	M10	120	50	25	34,68 €	48,59 €
VCMB10-140/B	VCMB10-140/SS/B	-	M10	140	50	25	44,28 €	53,09 €

Dimensions in mm