


- **Dual threaded screw wood/metal**
- Allows a metal object to be fixed to wood
- Materials:
  - Galvanised steel
  - Stainless steel, 304
- Supplied by the pack




### Mounting

- Screw should first be inserted into the wood using a suitable spanner
- Compatible with **N, SHN, NINA** and **NIN** nuts



Typical application



### DISCOUNTS Steel

Qty	1+	6+	20+	50+
Disc.	List	-10%	-20%	On request

### DISCOUNTS S/steel

Qty	1+	6+	10+
Disc.	List	-5%	On request

	Part number		ØF	L	Qty per pack		Price each 1 to 5	
	Steel	Stainless steel			Steel	S/steel	Steel	S/steel
VCMB5-40/B		-	M5	40	100	-	5,65 €	-
VCMB5-50/B		-	M5	50	100	-	9,36 €	-
VCMB6-60/B	VCMB6-60/SS/B		M6	60	100	100	11,00 €	36,38 €
VCMB6-80/B	VCMB6-80/SS/B		M6	80	100	100	18,18 €	45,69 €
VCMB6-100/B	VCMB6-100/SS/B		M6	100	100	100	29,76 €	61,45 €
VCMB6-120/B	VCMB6-120/SS/B		M6	120	100	100	30,83 €	69,20 €
VCMB8-50/B	VCMB8-50/SS/B		M8	50	100	100	11,75 €	96,98 €
VCMB8-60/B	VCMB8-60/SS/B		M8	60	100	100	12,67 €	57,14 €
VCMB8-80/B	VCMB8-80/SS/B		M8	80	100	50	16,68 €	38,27 €
VCMB8-100/B	VCMB8-100/SS/B		M8	100	100	50	20,78 €	51,87 €
VCMB8-120/B	VCMB8-120/SS/B		M8	120	100	50	25,32 €	60,40 €
VCMB8-140/B	VCMB8-140/SS/B		M8	140	100	50	32,73 €	70,23 €
VCMB8-160/B	VCMB8-160/SS/B		M8	160	100	50	36,56 €	69,36 €
VCMB10-60/B		-	M10	60	100	-	22,32 €	-
VCMB10-80/B	VCMB10-80/SS/B		M10	80	50	25	15,42 €	46,74 €
VCMB10-100/B	VCMB10-100/SS/B		M10	100	50	25	18,88 €	39,09 €
VCMB10-120/B	VCMB10-120/SS/B		M10	120	50	25	33,04 €	46,29 €
VCMB10-140/B	VCMB10-140/SS/B		M10	140	50	25	42,18 €	50,57 €

Dimensions in mm

## Our other products



TM\_CTM\_CTF

Suction cup threaded insert, Insert for suction cup - Tread click-in



G2

Steel spur gear, Steel 20NCD2



PRES2HR

Manual workbench press, Force up to 200kg



Q6

Deep groove ball bearing, Steel



UCF

Cast iron flange bearing unit, Cast iron



DOMI30

Accessories, Turntable



G3-ECO

Eco range Spur gear, Steel C45



NCT

Square tube connector, Fixed angle



PTMR

Telescopic furniture foot, threaded stud



Q7

Angular contact ball bearing, Steel



DKGS

Backlash free coupling Gerwah®,



RAM30

Manual bevel gearbox, Bevel

## Complementary products



VCMB

Dual-thread screw wood/metal, Steel



SHN

Hexagonal nut DIN934, A2 Stainless steel



NIN

Self-locking nut, A2 Stainless steel



SHW

Plain washer, A2 Stainless steel