

# Wing screw for safety washers



VPRHUSS

Hygienic Usit®

- Wing screw for use with Hygienic Usit® safety washers
- The wing screw makes perfect screw connections extremely easy.
- They can be easily opened or re-tightened without tools.
- Generous rounded form
- Fully polished surface, roughness less than Ra 0.8µm
- Material:  
Stainless steel 1.4404 (316L)  
Polished mirror finish




## Advantages

- Ideal for use in areas where there is contact with the product or inside aseptic isolators.
- Regardless of the mounting position of the wing screw, dirt and residue from products or cleaning materials will not be retained. This guarantees easy cleaning.
- The base of the wing screw is specially designed for an almost cavity-free seal of the screwed connection thus meeting hygiene requirements.

## Accessory

- RDE sealing washer (see pages 37 à 39)



## DISCOUNTS

Qty	1+	5+	10+	25+
Disc	Prix	-5%	-10%	On request

Part N°	ØD	ØD2	A	H	H1	B	R	L	L1	Price each
										1 to 4
VPR-4/HUSS	M4	10,8	20	19	5,3	4	0,45	8	7	19,18 €
VPR-5/HUSS	M5	11,8	21	21	6,0	5	0,50	10	9	20,19 €
VPR-6/HUSS	M6	14,2	25	25	7,0	6	0,55	12	11	22,57 €
VPR-8/HUSS	M8	18,0	33	33	8,4	8	0,60	16	15	30,25 €
VPR-10/HUSS	M10	22,3	40	40	10,0	10	0,75	20	19	47,90 €

All dimensions in mm

## Our other products



GBSz

Cylindrical ballscrew nut, Cylindrical leadscrew nut



G-ECO

Eco range Spur gear, Steel C45



T5P\_T10P

Connecting plate for T type timing belts, T5



SRG

Adjustable latch clamp with strike plate, Stroke from 117,4mm to 128mm



TCL-ECL

Support rod for heavy loads, Support spindle



PF60

Worm and wheel gear reducer, up to 118 Nm



DB

Steel bevel gear, 2:1



SSBRA

Stainless steel bevel gear, 1:1



HRV

V-rail guidance Simple Select®



MSP23

Masterplate® glueable insert Ø23,



CHA1056\_U4

Screw-in hinge, Section 40X40



BPLF

Ball transfer unit light duty, Light

## Complementary products



RDE-W

Sealing washer Hygienic Usit®, Stainless steel - White EPDM



RDE-B

Sealing washer Hygienic Usit®, Stainless steel - Blue EPDM