

# Symmetrical S shaped hook



## WSS

Wire diameter from 2mm to 8mm

- Low cost range of S shaped hooks
- White galvanized steel

### Application


- Not suitable for lifting applications

### Info

- Also available in stainless steel



Economy range



### DISCOUNTS

Qty	1+	80+	120+	160+	200+
Disc.	List	-10%	-15%	-20%	On request

Part number	ØD	L	M	Weight (g)	Qty per packet	Stock*	Price each 1 to 79
WSS2-30/B	2,0	20	2,5	2,0	40	✓	2,93 €
WSS2.5-33/B	2,5	27	3,5	3,0	40	-	3,45 €
WSS3-33/B	3,0	28	3,5	4,5	40	✓	3,45 €
WSS4-40/B	4,0	32	4,0	9,0	40	-	5,18 €
WSS5-47/B	5,0	38	5,0	17,0	20	✓	4,33 €
WSS6-61/B	6,0	50	7,0	31,0	10	-	3,45 €

\*Depending on availability - Dimensions in mm

HPC

WEB  
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

# Stalstock Symmetrical S shaped hook stainless steel

Wire diameter from 2mm to 8mm

WSSss

- Low cost range of S shaped hooks
- 304 stainless steel

## Application

- Not suitable for lifting applications


## Info

- Also available in normal steel

Stainless steel



Economy range



## DISCOUNTS

Qty	1+	80+	120+	160+	200+
Disc.	List	-10%	-15%	-20%	On request

Part number	ØD	L	M	Weight (g)	Qty per packet	Stock*	Price each 1 to 79
WSS2-30/SS/B	2,0	20	2,5	1,6	5	✓	1,51 €
WSS2.5-33/SS/B	2,5	27	3,5	2,8	5	-	2,47 €
WSS3-33/SS/B	3,0	28	3,5	4,0	5	✓	2,69 €
WSS4-40/SS/B	4,0	32	4,0	9,0	5	✓	5,89 €
WSS5-49/SS/B	5,0	38	5,0	17,0	5	✓	7,20 €
WSS6-63/SS/B	6,0	50	7,0	32,0	5	✓	8,43 €

\*Depending on availability - Dimensions in mm

## Our other products



PM2

Worm and wheel set,  
Non hardened steel



PRF\_ECL

Nut for aluminium  
profile, Steel square  
nut with tab



BAP25

Plastic clamping  
collar, Ø25 - Ø40




NPTR10

Adjustable cross  
clamp, Adjustable




GE

Toggle latches,  
Miniature



IN1

Internal gear,  
Machined plastic  
(delrin)



AF

Shaft clamp with  
keyway, Set screw



CFES

Eccentric cam  
follower, Eccentric




T5courroie

T type timing belt, T5  
Steel cored



ASM

Cylindrical polymer  
bush, Food grade



ACLBTS

Closing system for  
aluminium profile, 90°



BDP1R

Adjustable support  
arm, Single clamp

## Complementary products



WSSss

Symmetrical S shaped  
hook stainless steel,  
Stainless steel



FCHN\_CHNSS

Straight long link  
chain, Galvanised  
steel