

Symmetrical S shaped hook



WSS

Wire diameter from 2mm to 8mm

- Low cost range of S shaped hooks
- White galvanized steel

Application


- Not suitable for lifting applications

Info

- Also available in stainless steel



Economy range



DISCOUNTS

Qty	1+	80+	120+	160+	200+
Disc.	List	-10%	-15%	-20%	On request

Part number	ØD	L	M	Weight (g)	Qty per packet	Stock*	Price each 1 to 79
WSS2-30/B	2,0	20	2,5	2,0	40	✓	2,93 €
WSS2.5-33/B	2,5	27	3,5	3,0	40	-	3,45 €
WSS3-33/B	3,0	28	3,5	4,5	40	✓	3,45 €
WSS4-40/B	4,0	32	4,0	9,0	40	-	5,18 €
WSS5-47/B	5,0	38	5,0	17,0	20	✓	4,33 €
WSS6-61/B	6,0	50	7,0	31,0	10	-	3,45 €

*Depending on availability - Dimensions in mm

HPC

WEB
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

Stalstock Symmetrical S shaped hook stainless steel

Wire diameter from 2mm to 8mm WSSss

- Low cost range of S shaped hooks
- 304 stainless steel

Application

- Not suitable for lifting applications


Info

- Also available in normal steel

Stainless steel



Economy range



DISCOUNTS

Qty	1+	80+	120+	160+	200+
Disc.	List	-10%	-15%	-20%	On request

Part number	ØD	L	M	Weight (g)	Qty per packet	Stock*	Price each 1 to 79
WSS2-30/SS/B	2,0	20	2,5	1,6	5	✓	1,51 €
WSS2.5-33/SS/B	2,5	27	3,5	2,8	5	-	2,47 €
WSS3-33/SS/B	3,0	28	3,5	4,0	5	✓	2,69 €
WSS4-40/SS/B	4,0	32	4,0	9,0	5	✓	5,89 €
WSS5-49/SS/B	5,0	38	5,0	17,0	5	✓	7,20 €
WSS6-63/SS/B	6,0	50	7,0	32,0	5	✓	8,43 €

*Depending on availability - Dimensions in mm

Our other products



PRF_JL6
Lip seal for panel,
Door seal - Ø 6mm



CLG1
Moulded plastic spur
gear, Moulded plastic
(nylon)



LRRss
Latch, Spring loaded
latch - stainless steel



HRV
V-rail guidance
Simple Select®
system, Rail with
carriage



GCT
Pipe linch pin, Tube
linch pin



BEAS
Star shaped anti-
static handle, Star,
anti-static



GAL 42
Guide roller for plate
chain return, Without
ball bearing



PCS_PA6
Plastic sprocket,
12.7mm (DIN 08B-1)



GMC_GMK_BR
Guiding profile clamp,
Flat or rounded



V3RA_PT
3-spoked handwheel
with handle,
Polyamide



FR
Steel thread inserts,
Steel



PRF_CH
Cable-carrier chain for
aluminium profile,
Supplied in metre
lengths

Complementary products



WSSss
Symmetrical S shaped
hook stainless steel,
Stainless steel



FCHN_CHNss
Straight long link
chain, Galvanised
steel