

Plastic spur gear



Module 5.0


Machined Delrin



- Machined parts
- Precision class 9
- Pressure angle 20°
- Working temp. -50°C to +80°C

Option

- Different number of teeth: a datasheet is available in PDF on www.hpceurope.com



Torque indication	
For 50 teeth 1000 rpm	
Delrin	
Nm	90



DISCOUNTS

Qty	1+	4+	20+
Disc.	List -5%	On request	On request

Part number	Teeth Z	PCD ØP	Outside ØD	Boss ØM	Bore ØA	Price each 1 to 3	
						ZHG	ZHPG
ZHG5-12	12	60,00	70,00	40	20	On request	On request
ZHG5-14	14	70,00	80,00	50	25	On request	
ZHG5-15	15	75,00	85,00	50	25	On request	
ZHG5-18	18	90,00	100,00	70	30	92,30 €	
ZHG5-19	19	95,00	105,00	70	30	On request	
ZHG5-20	20	100,00	110,00	80	30	102,24 €	
ZHG5-21	21	105,00	115,00	80	30	On request	
ZHG5-22	22	110,00	120,00	80	30	On request	
ZHG5-23	23	115,00	125,00	85	30	113,49 €	
ZHG5-24	24	120,00	130,00	85	30	On request	
ZHG5-25	25	125,00	135,00	85	30	126,13 €	
ZHG5-30	30	150,00	160,00	100	30	191,17 €	
ZHG5-35	35	175,00	185,00	100	30	241,28 €	
ZHG5-38	38	190,00	200,00	100	38	On request	
ZHG5-40	40	200,00	210,00	150	38	On request	
ZHG5-42	42	210,00	220,00	150	38	On request	
ZHG5-45	45	225,00	235,00	150	38	On request	
ZHG5-50	50	250,00	260,00	150	38	On request	
ZHG5-52	52	260,00	270,00	150	38	On request	
ZHG5-55	55	275,00	285,00	150	38	On request	
↓ Gears available up to this size ↓							
ZHG5-115	115	575,00	585,00	Dimensions: contact us		On request	

Dimensions in mm

Our other products



PTMR

Telescopic furniture foot, threaded stud



SLBS

Stainless steel indexing plunger, Stainless steel



BFM

Flanged bronze nut, Bronze - 1 thread



SLB

Indexing plunger, stainless steel



SHSS

Shoulder screw stainless steel 416, Pre-treated 416 stainless steel



NPCR

Adjustable cell support, Adjustable



SVR20

Screwjack with travelling nut, with moving nut



DOMI120

Accessories, Clamping lever



CAP881

Side flexing slim slat top chain stainless




STU

Stroke rotary bushing, Steel



GLB

Small 6 lobe female handle,



B

Steel bevel gear, 1:1

Complementary products




HG5

Steel spur gear, Steel 20NC2



HG5-ECO

Eco range Spur gear, Steel C45



MR_MMR

Metric section rack, Steel