


Steel or stainless steel A2

**SHW
WM**

- **Conforms to DIN125**
- **Material:**
Zinc plated steel
Stainless steel A2 303/304
(working temperature:
up to +430°C)
- Sold by the packet

Option

- Also available in stainless steel 316 (A4)



DISCOUNTS

N° packs	1+	6+	11+
Discounts	List	-10%	On request

Part number	For thread ØM	ØD	L	Quantity per packet	Stock*	Price each 1 to 5
Steel						
WM-2/B	M2	5	0,3	200	-	3,10 €
WM-2.5/B	M2,5	6	0,5	200	-	2,33 €
WM-3/B	M3	7	0,5	200	-	2,48 €
WM-4/B	M4	9	0,8	200	✓	2,82 €
WM-5/B	M5	10	1,0	100	-	2,33 €
WM-6/B	M6	12	1,6	100	-	2,75 €
WM-8/B	M8	16	1,6	100	✓	3,30 €
WM-10/B	M10	20	2,0	100	✓	4,65 €
WM-12/B	M12	24	2,5	100	-	7,41 €
WM-14/B	M14	28	2,5	100	-	9,06 €
WM-16/B	M16	30	3,0	100	-	13,97 €
WM-20/B	M20	37	3,0	100	-	15,79 €
Stainless steel A2						
SHW-2/B	M2	5	0,3	2000	✓	10,37 €
SHW-2.5/B	M2,5	6	0,5	2000	✓	17,35 €
SHW-3/B	M3	7	0,5	1000	✓	2,73 €
SHW-4/B	M4	9	0,8	1000	✓	5,51 €
SHW-5/B	M5	10	1,0	1000	✓	7,59 €
SHW-6/B	M6	12	1,6	1000	✓	18,00 €
SHW-8/B	M8	16	1,6	500	✓	12,24 €
SHW-10/B	M10	20	2,0	500	✓	30,15 €
SHW-12/B	M12	24	2,5	200	✓	25,64 €
SHW-14/B	M14	28	2,5	200	✓	30,91 €
SHW-16/B	M16	30	3,0	200	✓	31,60 €
SHW-20/B	M20	37	3,0	200	✓	43,28 €

*Depending on availability - Dimensions in mm

Our other products



LVT

Miniature motorised actuator 2A, 2 ampers



CHM63

Worm and wheel gear reducer, up to 196 Nm



ETP

Modular handle for aluminium profile, Modular handle




SCE

U-shaped cable clamp, Steel



PTA80ssEB

Articulated foot with sheet metal base Ø80, Articulated foot



M1

Worm and wheel set, Machined plastic (delrin)



VDSQCB

Sliding lock adjustment system, Blocking wedge



SLB

Indexing plunger, steel class 5.8



LRRRA

Latch with locking system, Aluminium



BMM

Knurled knob - male, Knurled



CHAuss

Screwed hinge, 270°



PRS30

Stainless steel articulated foot Ø30, Ø 30

Complementary products



VTH

Hexagonal headed bolts, Steel class 8.8



SHN

Hexagonal nut DIN934, Steel (Class 6[8])



VCMB

Dual-thread screw wood/metal, Steel



BOX-WM

Box set of washer - DIN125, Box set of steel washers