



Plastic spur gear

Machined Delrin

Module
6.0

- Machined parts
- Precision class 9
- Pressure angle 20°
- Working temp. -50°C to +80°C

Option

- Different number of teeth: a datasheet is available in PDF on www.hpceurope.com


Torque indication	
For 50 teeth 1000 rpm	
Delrin	
Nm	140



ZHG



ZHPG (optional)



DISCOUNTS

Qty	1+	4+	20+
Disc.	List -5%	On request	On request

Part number	Teeth Z	PCD ØP	Outside ØD	Boss ØM	Bore ØA	Price each 1 to 3	
						ZHG	ZHPG
ZHG6-12	12	72,00	84,00	50	25	On request	On request
ZHG6-14	14	84,00	96,00	60	25	On request	On request
ZHG6-15	15	90,00	102,00	65	25	On request	On request
ZHG6-18	18	108,00	120,00	80	30	96,96 €	On request
ZHG6-19	19	114,00	126,00	80	30	On request	On request
ZHG6-20	20	120,00	132,00	90	30	107,74 €	On request
ZHG6-21	21	126,00	138,00	90	30	On request	On request
ZHG6-22	22	132,00	144,00	90	30	On request	On request
ZHG6-23	23	138,00	150,00	90	30	123,93 €	On request
ZHG6-24	24	144,00	156,00	90	30	On request	On request
ZHG6-25	25	150,00	162,00	90	30	134,69 €	On request
ZHG6-30	30	180,00	192,00	100	30	193,27 €	On request
ZHG6-31	31	186,00	198,00	100	30	On request	On request
ZHG6-32	32	192,00	204,00	120	38	On request	On request
ZHG6-35	35	210,00	222,00	120	38	300,64 €	On request
ZHG6-38	38	228,00	240,00	120	38	On request	On request
ZHG6-40	40	240,00	252,00	150	38	On request	On request
ZHG6-41	41	246,00	258,00	150	38	On request	On request
ZHG6-42	42	252,00	264,00	150	38	On request	On request
ZHG6-44	44	264,00	276,00	150	38	On request	On request
Gears available up to this size							
ZHG6-95	95	570,00	582,00	Dimensions: contact us		On request	On request


Dimensions in mm

On request


Our other products



RJA00_02
Sealing strip, Clipping



SUA4
Single chain supplied
by the metre, Steel



RPP14
RPP heavy duty
timing belt, RPP14



M1
Worm and wheel set,
Non hardened steel



EPE
Wing nuts Hygienic
Design®, Narrow



SDA
Locking bolt support
bracket, Mounting
holes parallel to
locating bolt



BAC105
Storage bin, 8mm



UTKpwc
Utilitrak® 3 wheels
carriage, Polymer
series V wheels



LFM
Steel leadscrew,
Medium carbon steel -
1 thread



PFC
Fixed rubber levelling
foot, Levelling support
for small parts



M2
Worm and wheel set,
Machined plastic
(delrin)



VTAP
Magnetic head screw,
With rubber coating
With rubber coating

Complementary products



HG6
Steel spur gear, Steel
20NCD2