


304L stainless steel

Module 0.5



- Quality standard 9
- Pressure angle 20°

Torque and power indication				
For 50 teeth at 1000 rpm				
	STS 304L	brass	fibre	
Nm	0.391	0.195	0.156	
kW	0.041	0.021	0.016	



stainless steel

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-12%	On request

Part number	Teeth Z	pcd ØP	Outside ØD	Boss ØM	Bore ØA	Price each 1 to 5
SSG0.5-12-304L	12	6	7	7	3	22,77 €
SSG0.5-15-304L	15	7,5	8,5	8,5	3	23,58 €
SSG0.5-16-304L	16	8	9	8,5	4	19,57 €
SSG0.5-18-304L	18	9	10	8,5	4	24,27 €
SSG0.5-20-304L	20	10	11	8,5	4	25,01 €
SSG0.5-22-304L	22	11	12	8,5	4	25,61 €
SSG0.5-24-304L	24	12	13	10	5	26,27 €
SSG0.5-25-304L	25	12,5	13,5	10	5	26,54 €
SSG0.5-26-304L	26	13	14	10	5	26,89 €
SSG0.5-28-304L	28	14	15	10	5	27,61 €
SSG0.5-30-304L	30	15	16	10	5	27,77 €
SSG0.5-32-304L	32	16	17	10	5	28,43 €
SSG0.5-36-304L	36	18	19	10	5	29,71 €
SSG0.5-40-304L	40	20	21	10	5	30,91 €
SSG0.5-44-304L	44	22	23	10	5	32,18 €
SSG0.5-48-304L	48	24	25	10	5	33,76 €
SSG0.5-50-304L	50	25	26	12	6	34,09 €
SSG0.5-54-304L	54	27	28	12	6	35,00 €
SSG0.5-56-304L	56	28	29	12	6	35,52 €
SSG0.5-60-304L	60	30	31	12	6	36,45 €
SSG0.5-64-304L	64	32	33	12	6	39,96 €
SSG0.5-70-304L	70	35	36	12	6	40,93 €
SSG0.5-80-304L	80	40	41	12	6	42,54 €
↓ Gears available up to this size ↓						
SSG0.5-278-304L	278	139	140	Dimensions: contact us		on request

*Depending on availability - Dimensions in mm

Our other products



STC

Shock Absorber - stop collar, Universal flange



BABam

Self-locking ball pin lifting ring for threaded hole, Self-locking



GE_C

Spherical bushing, Hard chromium / PTFE



PRF_BP

Doorstop for aluminium profile, Swing door stop




RIMtce

Locking castor, with central hole



EX

Optional shaft for E-type gear reducers, E Gearboxes single sided ou...



TBV

Manual lifting tables, 20kg



PRES2HR

Manual workbench press, Force up to 200kg



RFK28C

Hypoid gearbox - Stainless steel, up to



M1

Worm and wheel set, Bronze



PENV

Recessed handle, screw fixing



WS10

Drylin® W rail, Rail

Complementary products




ZG0

Plastic spur gear, Machined plastic (delrin)



SR

Narrow spur rack, Stainless steel



TR

Spur round rack, Stainless steel - module 0,25-1,5