


# T-type timing belts

Stock

## Pitch T5

Steel cored polyurethane

- Pitch 5mm
- Working temp. -30°C to +80°C
- Max. speed 40m/s
- Efficiency: up to 98%



### Options

- Belt by the metre **T5M**
- Alternative lengths/widths

### Accessories


- **BTE** arm and **GTC** roller belt tensioner

### Info.

- When ordering, add the width to the part number

Eg: **T5/120/4**

Compatible with  
T5 pulley



### DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-7%	On request

Part number	Length	Teeth	Stock*			Price each 1 to 5 for width				On request
			6mm	10mm	16mm	6mm	10mm	16mm	25mm	
T 5/150	150	30	✓	-	-	10,90 €	14,14 €	20,53 €		On request
T 5/185	185	37	✓	✓	✓	11,09 €	14,59 €	21,02 €		
T 5/200	200	40	✓	✓	✓	11,12 €	14,62 €	21,14 €		
T 5/210	210	42	-	✓	-	11,55 €	15,23 €	21,93 €		
T 5/215	215	43	-	-	-	11,22 €	14,84 €	21,35 €		
T 5/220	220	44	-	-	-	11,22 €	14,84 €	21,35 €		
T 5/225	225	45	✓	✓	✓	11,25 €	14,92 €	21,49 €		
T 5/245	245	49	✓	✓	-	11,36 €	15,14 €	21,76 €		
T 5/250	250	50	-	✓	-	11,77 €	15,61 €	22,41 €		
T 5/255	255	51	-	✓	-	11,41 €	14,41 €	21,86 €		
T 5/260	260	52	✓	-	-	11,41 €	15,14 €	21,86 €		
T 5/270	270	54	✓	✓	✓	11,46 €	15,24 €	21,95 €		
T 5/280	280	56	✓	✓	-	11,51 €	15,34 €	22,11 €		
T 5/295	295	59	-	✓	✓	11,61 €	15,54 €	22,33 €		

\*Depending on availability - Dimensions in mm

# Pitch T5

## DISCOUNTS

Qty	1+	6+	20+
Disc. List	-7%	On request	

Part number	Length	Teeth	Stock*	Stock*	Stock*	Price each 1 to 5 for width				
			6mm	10mm	16mm	6mm	10mm	16mm	25mm	
T 5/305	305	61	✓	✓	✓	11,71 €	15,64 €	22,51 €		
T 5/330	330	66	-	✓	✓	11,80 €	15,85 €	22,85 €		
T 5/340	340	68	✓	✓	-	11,80 €	15,92 €	22,95 €		
T 5/355	355	71	✓	✓	✓	11,93 €	16,17 €	23,25 €		
T 5/365	365	73	✓	✓	✓	11,97 €	16,19 €	23,42 €		
T 5/390	390	78	✓	✓	-	11,99 €	16,43 €	23,66 €		
T 5/400	400	80	✓	✓	-	12,10 €	16,51 €	23,76 €		
T 5/410	410	82	-	✓	✓	12,14 €	16,56 €	24,01 €		
T 5/420	420	84	✓	✓	✓	12,21 €	16,64 €	24,10 €		
T 5/455	455	91	✓	✓	✓	12,35 €	16,99 €	24,97 €		
T 5/460	460	92	-	-	-	12,78 €	17,57 €	25,76 €		
T 5/480	480	96	✓	✓	✓	12,43 €	17,36 €	25,47 €		
T 5/500	500	100	✓	✓	✓	12,56 €	17,55 €	25,95 €		
T 5/510	510	102	✓	-	-	12,58 €	17,70 €	26,20 €		
T 5/525	525	105	-	✓	✓	12,80 €	17,97 €	26,70 €		
T 5/545	545	109	-	✓	✓	13,06 €	18,18 €	27,20 €		
T 5/550	550	110	✓	✓	✓	13,06 €	18,18 €	27,20 €		
T 5/560	560	112	✓	✓	✓	13,13 €	18,34 €	27,42 €		
T 5/575	575	115	✓	✓	✓	13,35 €	18,67 €	27,94 €		
T 5/590	590	118	-	✓	-	13,80 €	19,44 €	29,33 €		
T 5/610	610	122	✓	✓	✓	13,69 €	19,11 €	28,89 €		
T 5/620	620	124	✓	-	-	13,78 €	19,25 €	29,18 €		
T 5/630	630	126	✓	✓	-	13,92 €	19,31 €	29,73 €		
T 5/650	650	130	-	-	✓	14,69 €	20,33 €	31,07 €		
T 5/690	690	138	-	✓	✓	14,77 €	20,47 €	31,38 €		
T 5/720	720	144	✓	-	✓	15,14 €	21,02 €	32,37 €		
T 5/750	750	150	-	✓	✓	15,54 €	21,58 €	33,34 €		
T 5/765	765	153	-	-	-	16,44 €	22,68 €	34,92 €		
T 5/780	780	156	-	-	✓	16,04 €	22,18 €	34,14 €		
T 5/815	815	163	-	✓	-	16,56 €	23,13 €	35,27 €		
T 5/840	840	168	-	-	-	16,81 €	23,57 €	36,00 €		
T 5/900	900	180	-	✓	-	17,70 €	24,97 €	37,76 €		
T 5/990	990	198	-	-	-	18,93 €	26,86 €	40,56 €		
T 5/1075	1075	215	-	-	-	20,19 €	27,96 €	43,81 €		
T 5/1100	1100	220	-	-	-	20,47 €	29,12 €	44,22 €		
T 5/1160	1160	232	-	-	-	22,27 €	31,30 €	47,56 €		
T 5/1215	1215	243	-	✓	✓	22,70 €	31,48 €	48,27 €		
T 5/1315	1315	263	-	-	-	25,80 €	34,92 €	52,80 €		
T 5/1380	1380	276	-	-	✓	26,33 €	35,23 €	53,15 €		

On request

\*Depending on availability - Dimensions in mm

## Our other products



BCA

Steel splined collar,  
Steel



PRF-SRA-78

Lock for aluminium  
profile, Quick fitting,  
self locking door lock



FRtool

Tool for thread repair  
inserts, Assembly tool




CHAR5050\_Z

Spring hinge, screwed



DILC

Indexing plunger with  
cam, with cam



CAB

Stainless steel cable,  
Stainless steel



NTMbr

Set screw brass tip,  
Brass-point



BUH77

Motor-gearbox 12V  
and 24V DC, from 0.1  
to 2 Nm



PF40

Worm and wheel gear  
reducer, up to 18 Nm



S\_2RS

Deep groove ball  
bearing, Stainless



PF30NM

Worm and wheel gear  
reducer, up to 8.8 Nm



MLY

Bow shackle with eye  
bolt, Steel

## Complementary products



GTC

Belt tensioner, For  
standard applications



T5-BAR

T type tooth bar  
stock, T5



T5-16ECO

T type timing pulley,  
Economy range - T5  
aluminium



T5M\_T10M

T type timing belt per  
metre, T5 Steel cored  
polyurethane