


# Mini leadscrew table with metric thread



## TBL

## Allows X-Y-Z movements


- Mini table with metric leadscrew for manual operation
- Metric leadscrew M6x1 right hand
- Guided by 2 steel rods on 4 brass bearings (no wiper joints)
- Axial precision < 0.10 mm
- With position indicator and button
- Material:  
Aluminium, steel
- Working temperature range: +5° to +80°C



Accurate to 0.1 mm



With Z Option :  
fixed via front plate



### DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-10%	On request

Part number	Stroke	Max supported load (kg)	Admissible torque (Nm)	Static force F (daN)	Weight (kg)	Price each
<b>Table horizontal X + Y axes</b>						
TBL-50-CV	50	1	0,50	6,00	0,25	297,76 €
TBL-100-CV	100	1	0,50	6,00	0,30	299,47 €
<b>Table vertical Z axis</b>						
TBL-50Z-CV	50	0,5	0,50	6,00	0,25	302,60 €
TBL-100Z-CV	100	0,5	0,50	6,00	0,30	304,33 €

Dimensions in mm

# Mini leadscrew table with metric thread

## TBL Base plate for X-Y-Z configurations

### - Connection plate



- To be screwed to end plates
- Countersunk mounting holes

### - Materials:

Anodised aluminium  
with plated steel screws


### XY configuration:

- 2 standard tables
- 1 base plate




### YZ configuration:

- 1 standard table
- 1 Z axis table
- 4 CHC screws (M4 x 20)



### XYZ configuration:

- 2 standard tables
- 1 Z axis table
- 1 base plate
- 4 CHC screws (M4 x 20)



### DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-10%	On request

Part number	For stroke (mm)	Price each
TBL-XY50	50	34,02 €
TBL-XY100	100	36,83 €

Dimensions in mm

## Our other products



DOMI80

Accessories, Clamping lever




BHEx

Hexagonal cap, Black technopolymer



BCM\_TP

Modular cylindrical brush, Tampico bristles



RDE-W

Sealing washer Hygienic Usit®, Stainless steel - White EPDM



GE

Toggle latches, Miniature



ZG2

Plastic spur gear, Machined plastic (delrin)



PRF-SCREEN-5

Screen support, Support with 5 axes of rotation



YG1

HEAVY DUTY spur gear, Steel 35NCD6



GARBAB

Lock pin for clamping, Ball lock pin



CHARcav

Spring hinge, to install



LVT


Miniature motorised actuator 2A, 2 amperes



PRF\_T

Corner reinforcement, Corner reinforcement

## Complementary products



TBL

Mini leadscrew table with metric thread, Base plate



TBEBASE10

Economic mini-table with trapezoidal leadscrew, 1kg



TBE12

Economic mini-table with trapezoidal leadscrew, 2kg



TBE16

Economic mini-table with trapezoidal leadscrew, 5kg