



Stainless steel/Polymer flanged bearing

4 mounting points

UCFPBT

- Self aligning bearing with 4 mounting points
- Interchangeable with cast iron units
- Grease applicator supplied
- Working temperature: -35°C to +102°C
- Materials:
 - Bearing: Stainless steel AISI 440C
 - Housing: PBT polymer
 - Grease: suitable for food industry



Colour

- UCF/PBT/G: green
- UCF/PBT/W: white

Accessory

- Protective cover

For the food industry




DISCOUNTS

| | | | | |
|-------|------|------|------|------------|
| Qty | 1+ | 10+ | 26+ | 51+ |
| Disc. | List | -10% | -20% | On request |

| Part number | ØD | A | E | G | L | ØS | Z | J | Bi | N | Stock* | Price each |
|--------------|----|-----|-------|------|------|----|------|------|------|------|--------|------------|
| UCF201/PBT/G | 12 | 86 | 63,5 | 13,4 | 27,8 | 11 | 36,3 | 18,0 | 31,0 | 12,7 | ✓ | 92,35 € |
| UCF202/PBT/G | 15 | 86 | 63,5 | 13,4 | 27,8 | 11 | 36,3 | 18,0 | 31,0 | 12,7 | ✓ | 87,89 € |
| UCF203/PBT/G | 17 | 86 | 63,5 | 13,4 | 27,8 | 11 | 36,3 | 18,0 | 31,0 | 12,7 | - | 82,15 € |
| UCF204/PBT/W | 20 | 86 | 63,5 | 13,4 | 27,8 | 11 | 36,3 | 18,0 | 31,0 | 12,7 | ✓ | 21,38 € |
| UCF205/PBT/W | 25 | 95 | 70,0 | 14,0 | 28,0 | 11 | 36,7 | 17,0 | 34,0 | 14,3 | ✓ | 27,95 € |
| UCF206/PBT/W | 30 | 107 | 83,0 | 14,3 | 31,5 | 11 | 41,4 | 19,2 | 38,1 | 15,9 | ✓ | 40,41 € |
| UCF207/PBT/W | 35 | 118 | 92,0 | 15,5 | 34,8 | 13 | 46,9 | 21,5 | 42,9 | 17,5 | - | 50,30 € |
| UCF208/PBT/W | 40 | 130 | 102,0 | 17,0 | 37,5 | 14 | 53,2 | 23,0 | 49,2 | 19,0 | ✓ | 61,54 € |

*Depending on availability - Dimensions in mm

Our other products



KS

Keysteel, Stainless steel - Keystock



PPJ

Indexing plunger with flange, With horizontal mounting flange and pu...



FBL6000_K19

Brush strip per meter horsehair fibres Ø0.2, Black horsehair




CMA

Eye bolt, Steel



PR40

Articulated foot Ø50, Ø 50



IN1

Internal gear, Machined plastic (delrin)



EIM

Stainless steel U bolt, Stainless steel



KH

Linear bearing, Light



G0

Steel spur gear, Steel 20NCD2



ACM_DZ

Clip for bonnet fastener, Clip



PRF-SCREEN-4

Screen support, Support with 4 axes of



SHTC

Drylin® Linear table, Maintenance free

Complementary products



UCF_PBT

Stainless steel/Polymer flanged bearing, Polymer and stainless steel



UCP_PBT

Stainless/Polymer pillow block bearing, Polymer and stainless steel



UCFL_PBT

Stainless steel/Polymer flanged bearing, Polymer and stainless steel



SBF

Open flange bearing unit for food industry, cover