

Stainless steel/Polymer flanged bearing

UCFLPBT

2 mounting points

- Self aligning bearing with 2 mounting points
- Interchangeable with cast iron units
- Grease applicator supplied
- Working temperature: -35°C to +102°C
- Materials:
 - Bearing: Stainless steel AISI 440C
 - Housing: PBT polymer
 - Grease: suitable for food industry




Colour

- UCFL/PBT/G: green
- UCFL/PBT/W: white

Accessory

- Protective cover

For the food industry



DISCOUNTS

Qty	1+	10+	26+	51+
Disc.	List	-10%	-20%	On request

Part number	ØD	A	E	ØB	G	L	ØS	Z	J	Bi	N	Stock*	Price each 1 to 9
UCFL201/PBT/G	12	113	90	65,0	11,4	26,5	11	33,7	15,4	31,0	12,7	✓	90,67 €
UCFL202/PBT/G	15	113	90	65,0	11,4	26,5	11	33,7	15,4	31,0	12,7	✓	86,30 €
UCFL203/PBT/G	17	113	90	65,0	11,4	26,5	11	33,7	15,4	31,0	12,7	-	82,15 €
UCFL204/PBT/W	20	113	90	64,0	11,4	26,5	11	33,7	15,4	31,0	12,7	✓	22,53 €
UCFL205/PBT/W	25	130	99	69,0	13,5	29,1	11	36,7	17,0	34,0	14,3	✓	26,17 €
UCFL206/PBT/W	30	148	117	80,0	13,3	30,5	11	41,2	19,0	38,1	15,9	-	34,91 €
UCFL207/PBT/W	35	164	130	90,0	16,1	32,8	13	43,4	18,0	42,9	17,5	-	49,62 €
UCFL208/PBT/W	40	176	144	100,0	20,0	37,5	14	51,7	21,5	49,2	19,0	-	58,94 €

*Depending on availability - Dimensions in mm

Our other products



DER90

Stainless steel AC asynchronous motor 1.1 - 1.5kW, 1.1 to 1.5kW



VELprf

Clip-on base for hook-and-loop strip, Polyamide




BHC

Socket head button screw, Stainless steel A2



PRF_ART

Articulated bracket for use with aluminium profile, With clamping ha...



KM

Bearing locknut, Locknut KM



DBL821

Idler for slat top chain, Range 821



SHTP

Drylin® Linear table, Economy range



EBC

Cap nut Hygienic Design®, Compact



HSE-HSB

Hexagonal spacer, Brass




PLM-SC

Magnetic stud with central countersunk hole, With milled bore



ATZYSS

Stainless steel diablo shaped elasto mount, Stainless steel



CHTRB


Single and dual output gearboxes, Up to 4,7 Nm

Complementary products



UCP_PBT

Stainless/Polymer pillow block bearing, Polymer and stainless steel



UCF_PBT

Stainless steel/Polymer flanged bearing, Polymer and stainless steel



SBF

Sealed flange bearing unit for Food Industry, cover



SBF

Sealed flange bearing unit for Food Industry, cover