

# Hand wheel with rotating handle



## VPRA<sub>M</sub>

## Thermosetting plastic

### - Hand wheel with handle for manual use

- Pre-bored
- Working temperature: -20°C to +140°C

### - Materials:

- Wheel: thermosetting plastic
- Hub: galvanised steel or stainless steel
- Handle: thermosetting plastic
- Axle: galvanised steel




### Options

- Different bore diameters
- Keyway
- See modification info

### Application

- All types of machines



### Bore modifications



### DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-5%	On request

Part number	ØD	H	L	C	B	ØA	Ød	E	F	P	ØN	Stock*	Price each 1 to 5
<b>Steel</b>													
VPRA50-M	50	23	50	11	10	16	4	9	20	13x27	M6	✓	16,05 €
VPRA65-M	65	28	55	13	13	20	4	10	24	13x27	M6	✓	18,66 €
VPRA80-M	80	31	71	14	15	20	4	10	27	17x40	M6	✓	20,48 €
VPRA100-M	100	35	85	14	16	24	4	11	29	21x50	M8	✓	25,30 €
VPRA125-M	125	44	99	16	18	32	6	13	35	23x55	M8	✓	32,48 €
VPRA150-M	150	48	113	18	20	32	6	13	37	25x65	M10	✓	39,91 €
VPRA200-M	200	58	143	21	24	40	6	16	44	28x85	M10	✓	63,04 €
VPRA250-M	250	66	151	22	30	48	6	17	49	28x85	M10	-	89,27 €
VPRA300-M	300	76	161	24	35	58	6	18	55	28x85	M10	-	138,16 €
<b>Stainless steel</b>													
VPRA100-M/SS	100	35	85	14	16	24	4	11	29	21x50	M8	-	44,21 €
VPRA150-M/SS	150	48	113	18	20	32	6	13	37	25x65	M10	-	58,95 €
VPRA200-M/SS	200	58	143	21	24	40	6	16	44	28x85	M10	-	86,02 €

\*Subject to availability - Dimensions in mm

## Our other products



KB\_WW  
Closed linear  
precision bearing,  
Economy range



CHINV2  
Invisible hinge,  
Invisible - Opening up  
to 125°



EMS  
Stainless steel knurled  
thumb nut, Knurled



BPTRW  
Cap for round tube to  
be welded, To be  
welded



PCLA\_T  
Technopolymer  
clamping lever - male,  
Plastic




SH2  
Parallel axis helical  
gear, Steel 20NCD2



RTN  
BoWex® curved tooth  
gear coupling, Nylon



SH1  
Parallel axis helical  
gear, Steel 20NCD2



CFC  
Spring loaded position  
switch, Electric



AT5courroie  
AT type timing belt,  
AT5 Steel cored



NPTR\_M  
Adjustable cross  
clamp, Adjustable



SFWR  
End support, Surface  
mounting

## Complementary products



MHQMEP  
Arm with rotating  
handle, Square bore



V3RA\_PT  
3-spoked handwheel  
with handle,  
Polyamide



SHA\_PTR  
Handwheel with  
folding handle,  
Polyamide



PGR  
Folding revolving  
handle for handwheel,  
Folding