

Manually operated wing nut

WING

Steel (ANSI B18-17) or
Stainless steel (DIN315/315)

- **Wing nut**

- **Materials:**


Steel wing nut (conforms to ANSI B18-17):

chromed forged steel

Stainless steel wing nut

(conforms to DIN314/315):

A2 stainless steel



DISCOUNTS

Qty per packs	1+	6+	20+	50+
Discounts	List	-5%	-20%	On request

Part number	Ød	Ød1	S	E	G	H	M	Qty per packs	Price each 1 to 5
Steel									
WING-M3/B	M3	7,5	-	18,5	-	8,8	3,0	500	46,18 €
WING-M4/B	M4	7,8	-	18,5	-	8,8	3,0	500	49,76 €
WING-M5/B	M5	9,5	-	22,5	-	10,5	3,8	500	51,19 €
WING-M6/B	M6	12,4	-	27,2	-	12,7	4,7	500	57,57 €
WING-M8/B	M8	13,5	-	30,0	-	14,6	5,6	200	30,05 €
WING-M10/B	M10	15,6	-	35,0	-	16,7	6,3	200	48,64 €
WING-M12/B	M12	20,5	-	47,6	-	22,3	7,5	100	53,29 €
A2 stainless steel									
WING-M3/SS/B	M3	6,8	4,5	15,3	1,2	7,2	2,4	100	13,61 €
WING-M4/SS/B	M4	8,0	5,2	17,6	1,6	8,6	2,9	100	12,98 €
WING-M5/SS/B	M5	10,3	6,7	22,5	2,1	11,0	4,1	100	14,14 €
WING-M6/SS/B	M6	12,7	8,4	27,8	2,5	13,6	5,1	100	20,01 €
WING-M8/SS/B	M8	13,8	9,1	30,3	2,8	14,8	5,6	100	28,23 €
WING-M10/SS/B	M10	16,5	11	36,2	3,3	17,7	6,8	100	50,21 €
WING-M12/SS/B	M12	22,5	15	49,4	4,5	24,1	9,0	50	53,53 €

Dimensions in mm

Our other products



BOX-TOR-G

Box set of Nitrile O-rings in nitrile, 3.00 x 1.50mm to 30.20 x 3.00




BOX-TOR-DRING

Box set of Nitrile D-rings NBR90Sh A, Flange seals



HLA24

Right angle spiro bevel gearbox, Up to 78Nm




PB

Plastic deep groove ball bearing, Plastic balls material : stainle...



PO

Pull handle - Multi-sector, Tapped recessed insert



PTGR

Tensioner pulley, For round belts



SSG2_304L

Stainless steel spur gear, Stainless steel 304L



COA-COG

Surface mounting plate, Surface mounting plate for ball joint



MEB

Moulded plastic bevel gear (nylon), 1:1



ZG125

Plastic spur gear, Machined plastic (delrin)



CHAPAMss

Weld-on hinge with flat end, Stainless steel or Aluminium



HTD8M_50

HTD Heavy duty timing pulley, HTD8 Cast

Complementary products



NIN

Self-locking nut, Steel



SHN

Hexagonal nut DIN934, Steel (Class 6[8])



CHC

Socket headed screw, Steel class 12.19



WINGbrEcrou

Manually tightened wing nut DIN315, Brass DIN 315