

# Wing screw, hand tightened **DIN316**

## WINGBR

## Brass


- Wing screw conforming to DIN316

- Material

Brass

### Advantages

- Easy hand tightening



### DISCOUNTS

Qty	1+	6+	11+
Disc.	Net	-10%	On request


Part N°	ØD	L	E	H	M	ØD1	ØS	Qty/pack	Price each	
									1 to 5	
WING-M4-10/BR/B	M4	10	20	10,5	4,6	8	7	100	40,03	€
WING-M4-16/BR/B	M4	16	20	10,5	4,6	8	7	100	65,78	€
WING-M4-20/BR/B	M4	20	20	10,5	4,6	8	7	100	82,43	€
WING-M5-10/BR/B	M5	10	26	13	6,5	11	9	100	83,14	€
WING-M5-16/BR/B	M5	16	26	13	6,5	11	9	100	88,64	€
WING-M5-20/BR/B	M5	20	26	13	6,5	11	9	100	99,40	€
WING-M5-25/BR/B	M5	25	26	13	6,5	11	9	100	105,13	€
WING-M5-30/BR/B	M5	30	26	13	6,5	11	9	100	116,66	€
WING-M6-16/BR/B	M6	16	33	17	8	13	11	100	97,91	€
WING-M6-20/BR/B	M6	20	33	17	8	13	11	100	114,75	€
WING-M6-25/BR/B	M6	25	33	17	8	13	11	100	122,15	€
WING-M6-30/BR/B	M6	30	33	17	8	13	11	100	129,99	€
WING-M6-40/BR/B	M6	40	33	17	8	13	11	100	153,23	€
WING-M8-10/BR/B	M8	10	39	20	10	16	12,5	50	145,45	€
WING-M8-16/BR/B	M8	16	39	20	10	16	12,5	50	163,93	€
WING-M8-20/BR/B	M8	20	39	20	10	16	12,5	50	177,81	€
WING-M8-25/BR/B	M8	25	39	20	10	16	12,5	50	190,69	€
WING-M8-30/BR/B	M8	30	39	20	10	16	12,5	50	202,99	€
WING-M8-40/BR/B	M8	40	39	20	10	16	12,5	50	243,49	€

All dimensions in mm

## Our other products



PV2R  
Adjustable suction-cup support,  
increased grip




PRF\_JL6  
Lip seal for panel,  
Door seal - Ø 6mm



PRS50  
Stainless steel  
articulated foot Ø50,  
Ø 50



E60  
Right angle helical  
reducers, from 4.50 to  
62 Nm



AWMP  
Aluminium shaft for  
linear guide,  
Aluminium



CLB\_T  
Die cast zinc clamping  
lever - male, Zamak




AC  
Strike for toggle latch,  
15mm



EHD06  
Internal epicyclic  
servo reducers, from  
8 to 19 Nm




DSF  
Slip friction clutch, 4  
to 2600 Nm



BMF  
Knurled knob -  
female, Knurled -



MDB\_MTB  
Moulded plastic bevel  
gear (nylon), 3:1



CRM  
Moulded nylon rack,  
Nylon

## Complementary products




VTHbr  
Hexagonal headed  
screw VTH - DIN933,  
Brass



WINGbr  
Wing screw, hand  
tightened DIN316,  
Brass DIN 316



SHNbr  
Hexagonal nut  
DIN934, Brass



SHWbr  
Washer - DIN125,  
Brass