

Wing screw, hand tightened **DIN316**

WINGBR

Brass


- Wing screw conforming to DIN316

- Material

Brass

Advantages

- Easy hand tightening




DISCOUNTS

Qty	1+	6+	11+
Disc.	Net	-10%	On request

Part N°	ØD	L	E	H	M	ØD1	ØS	Qty/pack	Price each	
									1 to 5	
WING-M4-10/BR/B	M4	10	20	10,5	4,6	8	7	100	40,03	€
WING-M4-16/BR/B	M4	16	20	10,5	4,6	8	7	100	65,78	€
WING-M4-20/BR/B	M4	20	20	10,5	4,6	8	7	100	82,43	€
WING-M5-10/BR/B	M5	10	26	13	6,5	11	9	100	83,14	€
WING-M5-16/BR/B	M5	16	26	13	6,5	11	9	100	88,64	€
WING-M5-20/BR/B	M5	20	26	13	6,5	11	9	100	99,40	€
WING-M5-25/BR/B	M5	25	26	13	6,5	11	9	100	105,13	€
WING-M5-30/BR/B	M5	30	26	13	6,5	11	9	100	116,66	€
WING-M6-16/BR/B	M6	16	33	17	8	13	11	100	97,91	€
WING-M6-20/BR/B	M6	20	33	17	8	13	11	100	114,75	€
WING-M6-25/BR/B	M6	25	33	17	8	13	11	100	122,15	€
WING-M6-30/BR/B	M6	30	33	17	8	13	11	100	129,99	€
WING-M6-40/BR/B	M6	40	33	17	8	13	11	100	153,23	€
WING-M8-10/BR/B	M8	10	39	20	10	16	12,5	50	145,45	€
WING-M8-16/BR/B	M8	16	39	20	10	16	12,5	50	163,93	€
WING-M8-20/BR/B	M8	20	39	20	10	16	12,5	50	177,81	€
WING-M8-25/BR/B	M8	25	39	20	10	16	12,5	50	190,69	€
WING-M8-30/BR/B	M8	30	39	20	10	16	12,5	50	202,99	€
WING-M8-40/BR/B	M8	40	39	20	10	16	12,5	50	243,49	€

All dimensions in mm

Our other products



T5M T10M

T type timing belt per metre, T5 Steel cored polyurethane



BLHB40

Right angled gearbox, bored shafts, up to 10.3 Nm



BOX-TOR-H

Box set of Nitrile O-rings in nitrile, 3.00 x 2.00mm to 45.20 x 4.00



EP7

Electronic digital position indicator, 5 numbers



ACL-PL

Joining plate for aluminium profile, joint plate - 86x86 mm



CHTRB

Single and dual output gearboxes, Up to 53,1 Nm



ABL100000

Antistatic brush, For sensitive surfaces




RVM14

Manual worm and wheel gearbox, Worm/wheel



PTA150

Articulated levelling foot, pressed base



BFD

Locking pin for bush, +180°C



GP75

Spring loaded toggle latch, Standard



BSB

Ball screw bearing unit, Support

Complementary products



VTHbr

Hexagonal headed screw VTH - DIN933, Brass



WINGbr

Wing screw, hand tightened DIN316, Brass DIN 316



SHNbr

Hexagonal nut DIN934, Brass



SHWbr

Washer - DIN125, Brass