

# Symmetrical S shaped hook



## WSS

Wire diameter from 2mm to 8mm

- Low cost range of S shaped hooks
- White galvanized steel

### Application


- Not suitable for lifting applications

### Info

- Also available in stainless steel



**Economy range**



### DISCOUNTS

Qty	1+	80+	120+	160+	200+
Disc.	List	-10%	-15%	-20%	On request

Part number	ØD	L	M	Weight (g)	Qty per packet	Stock*	Price each 1 to 79
WSS2-30/B	2,0	20	2,5	2,0	40	✓	2,93 €
WSS2.5-33/B	2,5	27	3,5	3,0	40	-	3,45 €
WSS3-33/B	3,0	28	3,5	4,5	40	✓	3,45 €
WSS4-40/B	4,0	32	4,0	9,0	40	-	5,18 €
WSS5-47/B	5,0	38	5,0	17,0	20	✓	4,33 €
WSS6-61/B	6,0	50	7,0	31,0	10	-	3,45 €

\*Depending on availability - Dimensions in mm

**HPC**

WEB  
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

# Stalstock Symmetrical S shaped hook stainless steel

Wire diameter from 2mm to 8mm

WSSss

- Low cost range of S shaped hooks
- 304 stainless steel

## Application

- Not suitable for lifting applications


## Info

- Also available in normal steel

Stainless steel



Economy range



## DISCOUNTS

Qty	1+	80+	120+	160+	200+
Disc.	List	-10%	-15%	-20%	On request

Part number	ØD	L	M	Weight (g)	Qty per packet	Stock*	Price each 1 to 79
WSS2-30/SS/B	2,0	20	2,5	1,6	5	✓	1,51 €
WSS2.5-33/SS/B	2,5	27	3,5	2,8	5	-	2,47 €
WSS3-33/SS/B	3,0	28	3,5	4,0	5	✓	2,69 €
WSS4-40/SS/B	4,0	32	4,0	9,0	5	✓	5,89 €
WSS5-49/SS/B	5,0	38	5,0	17,0	5	✓	7,20 €
WSS6-63/SS/B	6,0	50	7,0	32,0	5	✓	8,43 €

\*Depending on availability - Dimensions in mm

## Our other products



MDB\_MTB

Moulded plastic bevel gear (nylon), 3:1



AT10-32ECO

AT type timing pulley, Economy range - AT10 aluminium



PX

Optional output shaft stainless steel, P gearboxes single sided outp...



GG1

Ground spur gear, Heat treated steel




RCX-6

Spherical tilt washer - DIN6319, convex



WJRM

Drylin® W hybrid bearing block, Hybrid bearings



RPP8

RPP heavy duty timing belt, RPP8



FBL6000\_K19

Brush strip per meter horsehair fibres Ø0.2, Black horsehair



VTAP

Magnetic head screw, With rubber coating With rubber coating



TPEpbd

Castor for aluminium profile, Swivel with brake



AT10courroie

AT type timing belt, AT10 Steel cored polyurethane



HSSss

Stainless steel shoulder screw ISO7379, Stainless steel ISO 7379

## Complementary products



WSSss

Symmetrical S shaped hook stainless steel, Stainless steel



FCHN\_CHNss

Straight long link chain, Galvanised steel