

Plastic spur gear



Module 5.0


Machined Delrin



- Machined parts
- Precision class 9
- Pressure angle 20°
- Working temp. -50°C to +80°C

Option

- Different number of teeth: a datasheet is available in PDF on www.hpceurope.com



Torque indication	
For 50 teeth 1000 rpm	
Delrin	
Nm	90



DISCOUNTS

Qty	1+	4+	20+
Disc.	List -5%	On request	

Part number	Teeth Z	PCD ØP	Outside ØD	Boss ØM	Bore ØA	Price each 1 to 3	
						ZHG	ZHPG
ZHG5-12	12	60,00	70,00	40	20	On request	
ZHG5-14	14	70,00	80,00	50	25	On request	
ZHG5-15	15	75,00	85,00	50	25	On request	
ZHG5-18	18	90,00	100,00	70	30	92,30 €	
ZHG5-19	19	95,00	105,00	70	30	On request	
ZHG5-20	20	100,00	110,00	80	30	102,24 €	
ZHG5-21	21	105,00	115,00	80	30	On request	
ZHG5-22	22	110,00	120,00	80	30	On request	
ZHG5-23	23	115,00	125,00	85	30	113,49 €	
ZHG5-24	24	120,00	130,00	85	30	On request	
ZHG5-25	25	125,00	135,00	85	30	126,13 €	
ZHG5-30	30	150,00	160,00	100	30	191,17 €	
ZHG5-35	35	175,00	185,00	100	30	241,28 €	
ZHG5-38	38	190,00	200,00	100	38	On request	
ZHG5-40	40	200,00	210,00	150	38	On request	
ZHG5-42	42	210,00	220,00	150	38	On request	
ZHG5-45	45	225,00	235,00	150	38	On request	
ZHG5-50	50	250,00	260,00	150	38	On request	
ZHG5-52	52	260,00	270,00	150	38	On request	
ZHG5-55	55	275,00	285,00	150	38	On request	
↓ Gears available up to this size ↓							
ZHG5-115	115	575,00	585,00	Dimensions: contact us		On request	

Dimensions in mm

On request

Our other products



BLM
Spring loaded plunger with ball tip, Stainless steel body



FAD
Threaded swivel feet, Swivel feet without anti-slip plate



ACL-PR
Joining plate for aluminium profile, Right angled connection




BSPM
Miniature ballscrew, Nut+rolled ballscrew



LRR
Spring loaded latch, Spring loaded latch



SHA
Handwheel without handle, Polyamide



RPPM
RPP type belt per metre, RPP8 Steel cored polyurethane



BIMSS
Indexing plunger mini, miniature - Stainless steel



BPMc
Stainless steel slotted spring plunger with ceramic ball tip, 303 St...



SEV
Vertical stirrup toggle clamp, Vertical Latch Clamp - stainless steel



CMM
Male rod ends DIN ISO12240-4, Steel / bronze



VBFP
Small 6 lobe threaded handle - female, Duroplast - Stainless steel


Complementary products



HG5
Steel spur gear, Steel 20NCD2



HG5-ECO
Eco range Spur gear, Steel C45



MR_MMR
Metric section rack, Steel