

Plastic spur gear



Module 5.0


Machined Delrin



- Machined parts
- Precision class 9
- Pressure angle 20°
- Working temp. -50°C to +80°C

Option

- Different number of teeth: a datasheet is available in PDF on www.hpceurope.com



Torque indication	
For 50 teeth 1000 rpm	
	Delrin
Nm	90



DISCOUNTS

Qty	1+	4+	20+
Disc.	List -5%	On request	On request

Part number	Teeth Z	PCD ØP	Outside ØD	Boss ØM	Bore ØA	Price each 1 to 3	
						ZHG	ZHPG
ZHG5-12	12	60,00	70,00	40	20	On request	On request
ZHG5-14	14	70,00	80,00	50	25	On request	
ZHG5-15	15	75,00	85,00	50	25	On request	
ZHG5-18	18	90,00	100,00	70	30	92,30 €	
ZHG5-19	19	95,00	105,00	70	30	On request	
ZHG5-20	20	100,00	110,00	80	30	102,24 €	
ZHG5-21	21	105,00	115,00	80	30	On request	
ZHG5-22	22	110,00	120,00	80	30	On request	
ZHG5-23	23	115,00	125,00	85	30	113,49 €	
ZHG5-24	24	120,00	130,00	85	30	On request	
ZHG5-25	25	125,00	135,00	85	30	126,13 €	
ZHG5-30	30	150,00	160,00	100	30	191,17 €	
ZHG5-35	35	175,00	185,00	100	30	241,28 €	
ZHG5-38	38	190,00	200,00	100	38	On request	
ZHG5-40	40	200,00	210,00	150	38	On request	
ZHG5-42	42	210,00	220,00	150	38	On request	
ZHG5-45	45	225,00	235,00	150	38	On request	
ZHG5-50	50	250,00	260,00	150	38	On request	
ZHG5-52	52	260,00	270,00	150	38	On request	
ZHG5-55	55	275,00	285,00	150	38	On request	
↓ Gears available up to this size ↓							
ZHG5-115	115	575,00	585,00	Dimensions: contact us		On request	

Dimensions in mm

Our other products



ACAss

Stainless steel splined shaft, Stainless steel



BL8

Right angled gearbox, from 0.20 to 2 Nm



KSM

Cylindrical steel nut, Steel - 1 thread



SSB

Stainless steel bevel gear, 1:1



UGH16

H Type Guide units, For Ø12 and Ø16 actuators




RJA11_27

Sealing strip, Not clipping



T5M T10M

T type timing belt per metre, T10 Steel cored polyurethane



H1

Crossed helical gear crossed axis at 90°, Machined plastic (delrin)



TCSH

Automatic chain tensioner, With



TAC

Rigging screw (hook/eye), Steel



BSB

Ballscrew bearing unit, Support



DCG

Suction cup, 2.5 bellows, silicon

Complementary products




HG5

Steel spur gear, Steel 20NCD2



HG5-ECO

Eco range Spur gear, Steel C45



MR_MMR

Metric section rack, Steel