


Rapport 4:1

Acier 60C40

- Module 0,8 à 6
- Angle de pression 20°
- Denture Gleason
- Matière :
Acier 60C40
- Pour un couple, il faut deux pièces



Les chiffres du couple sont doublés lors d'un traitement thermique

INDICATION DE COUPLE ET DE PUISSANCE		Pour 20 dents à 1000 t/min.									
		6 MOD	5 MOD	4 MOD	3 MOD	2,5 MOD	2 MOD	1,5 MOD	1,25 MOD	1 MOD	0,8 MOD
Couple (Nm)		51,00	32,00	16,40	7,70	4,30	2,20	0,94	0,71	0,57	0,14
Puissance (kW)		5.35	3.35	1.72	0.81	0.455	0.231	0.097	0.08	0.03	0.015

REMISES

Qté	1+	6+	20+	40+
Rem. Prix	-5%	-10%	-10%	Sur demande

Références	Dents Z	Mod	ØP	E	ØD	ØA	ØM	F	G	H	Vis R	T	Prix Un. 1 à 5
FB0.8-15	15	0,8	12,0	35,0	14,23	6	10	18,07	10,58	7,10	M3	5	26,70 €
FB0.8-60	60		48,0	20,0	48,22	8	30	15,98	8,00	7,10	M3	4	40,58 €
FB1-15	15	1,0	15,0	45,0	17,79	8	13	24,22	14,73	9,28	M4	7	29,87 €
FB1-60	60		60,0	30,0	60,27	10	40	25,08	12,00	9,28	M4	6	43,34 €
FB1.5-15	15	1,5	22,5	60,0	26,69	10	18	28,82	12,08	13,91	M4	6	31,22 €
FB1.5-60	60		90,0	35,0	90,41	15	50	27,61	12,00	13,91	M4	6	48,32 €
FB2-15	15	2,0	30,0	76,1	35,57	12	24	33,05	15,36	17,00	M5	10	
FB2-60	60		120,0	45,0	120,55	18	60	34,81	19,00	17,00	M5	10	
FB2.5-15	15	2,5	37,5	94,0	44,46	15	30	39,95	17,00	21,00	M6	12	
FB2.5-60	60		150,0	55,0	150,69	20	75	42,20	23,00	21,00	M6	12	
FB3-15	15	3,0	45,0	112,0	53,55	18	36	47,90	21,00	26,00	M6	12	
FB3-60	60		180,0	65,0	180,82	25	90	49,83	27,00	26,00	M6	12	
FB4-15	15	4,0	60,0	146,0	71,14	20	48	59,90	25,00	34,00	M8	15	
FB4-60	60		240,0	82,0	241,10	30	120	61,61	35,00	34,00	M8	15	
FB5-15	15	5,0	75,0	175,0	88,92	20	60	64,98	23,00	40,00	M8	15	
FB5-60	60		300,0	90,0	301,37	35	160	64,00	28,00	40,00	M10	15	
FB6-15	15	6,0	90,0	205,0	106,70	25	75	70,12	23,00	45,00	M10	15	
FB6-60	60		360,0	96,0	361,64	40	180	64,16	28,00	45,00	M10	15	

Dimensions en mm

Sur demande