



**SKM**  
**SKF**



## Bouton étoile mâle ou femelle

### Tarudage ou filetage M4 à M10

- Avec insert mâle ou femelle acier
- Matière : plastique phénolique noir
- T° d'utilisation : -30°C à +140°C

#### Avantages

- Bonne préhension



#### REMISES

Qté	1+	10+	20+	50+	100+	200+
Rem.	-20%	-30%	-40%	-50%	Sur demande	

Références	Filetage ØT	L	ØA	ØD	H	Stock*	Prix Uni. 1 à 9
<b>Mâle</b>							
SK4M	M4	10,0	10	20	17	✓	3,03 €
SK10M	M5	10,0	12	25	16	✓	1,72 €
SK15M	M6	15,0	14	32	20	✓	1,81 €
SK20M	M8	20,0	16	40	25	✓	2,76 €
SK30M	M10	30,0	21	50	32	✓	4,44 €
<b>Femelle</b>							
SK4F	M4	8,0	10	20	17	✓	2,27 €
SK10F	M5	9,0	12	25	16	✓	2,27 €
SK15F	M6	13,5	14	32	20	✓	2,08 €
SK20F	M8	16,0	16	40	25	✓	3,25 €
SK30F	M10	21,0	21	50	32	✓	4,48 €

\*Dans la limite du disponible