


- Module 0,8 à 6
- Angle de pression 20°
- Matière : acier 60C40
- Pour un couple, il faut deux pièces



Les chiffres du couple sont doublés lors d'un traitement thermique

INDICATION DE COUPLE ET DE PUISSANCE	Pour 20 dents à 1000 t/min.									
	6 MOD	5 MOD	4 MOD	3 MOD	2,5 MOD	2 MOD	1,5 MOD	1,25 MOD	1 MOD	0,8 MOD
Couple (Nm)	51,00	32,00	16,40	7,70	4,30	2,20	0,94	0,71	0,57	0,14
Puissance (kW)	5,35	3,35	1,72	0,81	0,455	0,231	0,097	0,08	0,03	0,015

REMISES

Qté	1+	6+	20+	40+	60+	100+
Rem. Prix	-5%	-10%	-15%	-20%	Sur demande	

Références	Dents		ØP	E	ØD	ØA	ØM	F	G	H	Vis		Prix Uni. 1 à 5
	Z	Mod									R	T	
TB0,8-15	15	0,8	12,0	28	14,14	6	10	15,63	9,67	5,69	M3	5,0	21,19 €
TB0,8-45	45		36,0	20	36,30	8	28	16,07	8,00	5,69	M3	4,0	31,91 €
TB1-15	15	1,0	15,0	32	17,67	8	13	16,54	9,18	7,12	M4	4,5	23,05 €
TB1-45	45		45,0	24	45,37	10	40	19,09	10,00	7,12	M4	5,0	34,16 €
TB1,5-15	15	1,5	22,5	45	26,51	10	18	21,80	10,51	10,67	M4	5,0	23,64 €
TB1,5-45	45		67,5	32	68,06	15	50	24,63	12,00	10,67	M4	6,0	38,76 €
TB2-15	15	2,0	30,0	62	35,37	12	24	31,77	16,00	15,00	M5	10,0	45,75 €
TB2-45	45		90,0	42	90,74	18	48	32,39	18,00	15,00	M5	10,0	151,65 €
TB2,5-15	15	2,5	37,5	75	44,21	18	30	36,52	18,00	18,00	M6	12,0	59,13 €
TB2,5-45	45		112,5	50	113,43	20	55	37,77	22,00	18,00	M6	12,0	189,86 €
TB3-15	15	3,0	45,0	88	53,05	18	36	42,20	19,00	22,00	M6	12,0	81,26 €
TB3-45	45		135,0	58	136,11	23	65	43,45	24,00	22,00	M6	12,0	225,39 €
TB4-15	15	4,0	60,0	115	70,74	20	48	54,55	23,00	30,00	M8	15,0	90,81 €
TB4-45	45		180,0	75	181,48	30	85	55,77	30,00	30,00	M8	15,0	278,09 €
TB5-15	15	5,0	75,0	138	88,42	20	60	64,75	23,00	40,00	M8	15,0	137,63 €
TB5-45	45		225,0	86	226,85	35	120	62,68	28,00	40,00	M10	15,0	336,18 €
TB6-15	15	6,0	90,0	160	106,11	25	72	69,31	22,00	45,00	M10	15,0	172,62 €
TB6-45	45		270,0	95	272,22	40	140	66,17	28,00	45,00	M10	15,0	403,79 €