


- **Vis moletée monobloc**
- Élément de manœuvre
- Matière : inox 303 poli
- Selon DIN 464
- **Pour cette longueur, la vis moletée est livrée avec tige complète (pas de gorge de dégagement)



REMISES

Qté	1+	6+	20+	40+	60+	101+
Rem.	-10%	-15%	-20%	-25%	Sur demande	

Références	ØD1	ØD2	ØD3	H	K	L	Stock*	Prix Uni. 1 à 5
VMS4-10	M4	16	8	9,5	3,5	10	✓	2,27 €
VMS4-16	M4	16	8	9,5	3,5	16	✓	2,50 €
VMS4-20	M4	16	8	9,5	3,5	20**	✓	2,74 €
VMS5-10	M5	20	10	11,5	4,0	10	✓	2,78 €
VMS5-16	M5	20	10	11,5	4,0	16	✓	3,31 €
VMS5-20	M5	20	10	11,5	4,0	20**	✓	3,99 €
VMS6-10	M6	24	12	15,0	5,0	10	✓	5,96 €
VMS6-16	M6	24	12	15,0	5,0	16	✓	4,64 €
VMS6-20	M6	24	12	15,0	5,0	20	✓	8,37 €
VMS6-25	M6	24	12	15,0	5,0	25**	✓	6,81 €
VMS8-16	M8	30	16	18,0	6,0	16	✓	10,59 €
VMS8-20	M8	30	16	18,0	6,0	20	✓	11,47 €
VMS8-25	M8	30	16	18,0	6,0	25	✓	10,90 €
VMS10-20	M10	36	20	23,0	8,0	20	✓	16,11 €
VMS10-25	M10	36	20	23,0	8,0	25	✓	18,12 €

*Dans la limite du disponible