

# Mounting feet with integrated castors

## Offset castor

## PDR


- Combines the advantages of a static mounting foot and a castor
- Use a hexagonal spanner to release the castor
- Castor protrudes 12.5mm when released
- Only for use on surfaces that are smooth (crevices less than 5mm) and horizontal (max slope 3°)
- Max static load 2,500 kg per foot
- Max load 200 kg per foot if used in movable mode
- Materials:
  - Base - Polyamide
  - Sole - NBR rubber
  - Threaded shaft - Chromed steel

### Typical application


- A vessel remains static whilst the product within is processed but once empty, can be moved for cleaning purposes.

### Advantages

- Flexibility (1 item performs 2 functions)
- Less manoeuvring to move a structure
- Time saving



Retracting the castor



### DISCOUNTS

| Qty   | 1+   | 6+  | 10+        |
|-------|------|-----|------------|
| Disc. | List | -5% | On request |

| Part number                        | ØM            | L   | Load Castor fixed (static) (kg) | Load Castor free (dynamic) (kg) | Price each 1 to 5 |
|------------------------------------|---------------|-----|---------------------------------|---------------------------------|-------------------|
| <b>With threaded shaft</b>         |               |     |                                 |                                 |                   |
| PDR100-16-50/RD                    | M16           | 50  | 2500                            | 200                             | 118,60 €          |
| PDR100-16-100/RD                   | M16           | 100 | 2500                            | 200                             | 122,18 €          |
| PDR100-20-75/RD                    | M20           | 75  | 2500                            | 200                             | 122,18 €          |
| PDR100-20-125/RD                   | M20           | 125 | 2500                            | 200                             | 125,78 €          |
| PDR100-24-75/RD                    | M24           | 75  | 2500                            | 200                             | 122,18 €          |
| PDR100-24-125/RD                   | M24           | 125 | 2500                            | 200                             | 125,78 €          |
| <b>With 80x80mm mounting plate</b> |               |     |                                 |                                 |                   |
| PDR100-80-80/RD                    | 4x8.5mm holes |     | 2500                            | 200                             | 122,18 €          |

Dimensions in mm

**0 825 88 6000**  
Service 0,15 € / min  
+ prix appel