

Castor with central hole

RBGTC For medium loads up to 110kg

- **Light industrial swivel castor with central hole**
- Swivel system uses two ball races
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Materials:
 - Top plate: pressed steel sheet, protected by bright zinc plating
 - Grey vulcanized rubber wheel 85°Shore (see RBG)
 - Smooth central bore
- Working temperature range: - 20°C to + 60°C

Advantages

- Soft, silent wheel
- Absorbs shock and vibration
- Will not damage floors

Swivel



ØD



B



H



ØE



ØK

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	ØE	Swivel interference ØK	Max load (kg)	Stock*	Price each 1 to 9
Swivel								
RBG50/TC/P	50	22	76	10	98	45	✓	3,91 €
RBG60/TC/P	60	24	85	10	110	55	✓	4,44 €
RBG80/TC/P	80	23	105	10	138	65	✓	5,71 €
RBG100/TC/P	100	26	121	10	166	75	✓	6,97 €
RBG125/TC/P	125	32	158	13	216	110	✓	10,68 €
Swivel with double lock								
RBG50/TC/PDB	50	22	76	10	172	45	4	5,79 €
RBG60/TC/PDB	60	24	85	10	172	55	4	6,00 €
RBG80/TC/PDB	80	23	105	10	188	65	✓	7,19 €
RBG100/TC/PDB	100	26	121	10	188	75	✓	10,20 €
RBG125/TC/PDB	125	32	158	13	220	110	✓	14,95 €

Dimensions in mm