

Rubber castor with central hole

RBNTC

For heavy loads up to 215kg


- **Industrial wheel suitable for loads up to 215kg**
- Swivel system uses two ball races
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- **Materials:**
 - Baseplate: pressed steel sheet, protected by bright zinc plating
 - Black vulcanized rubber wheel 85°Shore (see RBN)
- Smooth central bore
- Working temperature range: - 20°C to + 60°C



Swivel with double locks

Advantages

- Soft and silent
- Absorbs shock and vibration
- Will not damage floors



DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	ØE	Swivel interference ØK	Maximum load (kg)	Price each 1 to 9
Swivel							
RBN80/TC/P	80	34	105	12	158	75	9,76 €
RBN100/TC/P	100	35	125	12	182	100	10,76 €
RBN125/TC/P	125	38	152	12	210	125	13,31 €
RBN150/TC/P	150	40	179	12	242	150	17,17 €
RBN160/TC/P	160	38	188	12,5	267	150	24,29 €
RBN200/TC/P	200	47	232	12,5	320	215	29,54 €
Swivel with double lock							
RBN80/TC/PDB	80	34	105	12	290	75	14,96 €
RBN100/TC/PDB	100	35	125	12	290	100	15,80 €
RBN125/TC/PDB	125	38	152	12	290	125	18,40 €
RBN150/TC/PDB	150	40	179	12	290	150	23,29 €
RBN160/TC/PDB	160	38	188	12,5	267	150	36,40 €
RBN200/TC/PDB	200	47	232	12,5	320	215	42,12 €

Dimensions in mm