

# Polyamide castor with central hole, stainless steel


For heavy loads up to 600kg

RPC TCSS

- Industrial wheel suitable for loads up to 600kg
- Swivel system uses two ball races
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Smooth central bore
- Materials:
  - Top plate: pressed stainless steel sheet
  - Polyamide wheel (see RPC)
  - Working temperature range: - 30°C to + 80°C

## Advantages

- Light
- Will not mark or stain floor
- Low rolling resistance
- For solid, hard floors
- Ideal for use in wet and dirty environments (fish markets, butcher shops, canneries)



## DISCOUNTS

Qty	1+	5+	15+
Disc.	List	-5%	On request

Part number	ØD	B	H	ØE	Swivel interference	Max load (kg)	Price each 1 to 9
<b>Swivel</b>							
RPC60/TC/P/SS	60	31	96	12	155	200	25,19 €
RPC80/TC/P/SS	80	32	109	12	173	250	25,19 €
RPC100/TC/P/SS	100	32	124	12	193	300	26,97 €
RPC125/TC/P/SS	125	36	152	12	221	350	31,46 €
RPC150/TC/P/SS	150	37	179	12	257	400	55,84 €
RPC160/TC/P/SS	160	40	197	12,5	268	600	72,57 €
RPC200/TC/P/SS	200	50	240	12,5	318	700	77,38 €
<b>Swivel with double brake</b>							
RPC80/TC/PDB/SS	80	32	109	12	173	250	34,45 €
RPC100/TC/PDB/SS	100	32	124	12	193	300	36,30 €
RPC125/TC/PDB/SS	125	36	152	12	221	350	38,70 €
RPC150/TC/PDB/SS	150	37	179	12	257	400	75,28 €
RPC160/TC/PDB/SS	160	40	197	12,5	268	600	88,52 €
RPC200/TC/PDB/SS	200	50	240	12,5	318	700	98,97 €

Dimensions in mm

**0 825 88 6000**  
Service 0,15 € / min  
+ prix appel

Fax

cial2@hpceurope.com

**HPC** SUPPLEMENT 2019

269